



## Public Safety BDA for 700 AND 800 MHZ 2W CLASS B AC

- Compact, high-performance, economical public safety signal source
- UL2524 Certified – UL File S36319
- High performance architecture that supports up to 3 wide band filters
- Automatic Gain Control (AGC) and band selective uplink squelch ensure clear voice transmission
- Output power and band capacity can be field-upgraded via license key
- Web-based GUI and SNMP support for intelligent configuration and monitoring
- NFPA 1221 and IFC compliant
- Automatic oscillation detection and self-healing mechanism
- Built-in automatic donor antenna supervision
- Short installation time due to built-in isolation test, alarm test and one click summary report

## Product Classification

**Product Type** Public safety RF repeater unit

## General Specifications

**Antenna Interface at Repeater** 4.3-10

**Indoor Antenna** Optional, not included

**Performance Note** Values typical, unless otherwise stated

**Supervision/Control Option** Dry alarm contacts with 2.2k Ohm EOL resistors | Remote control via Ethernet

## Dimensions


**Height** 480 mm | 18.898 in

**Width** 400 mm | 15.748 in

**Depth** 170 mm | 6.693 in

**Optional Antenna Length** 90 mm | 3.543 in

## Outline Drawing



## Electrical Specifications

### Electrical Safety Standard

UL 2524 Certified | UL 62368 | US FCC Part 20 | US FCC Part 90

### Gain, typical

90 dB

### Gain Adjustment Range

30 dB

### License Band

700 (including FirstNet) | 800

### Local Power

110 Vac

### Mains Power

110VAC/60Hz

### Return Loss

13 dB

### Power Consumption

130 W

## Electrical Specifications, Rx (Uplink)

### Operating Frequency Band

788 – 798 MHz (FirstNet) | 788 – 805 MHz | 806 – 824 MHz

### Output Power @ One Carrier

27 dBm

### Output Power @ Two Carriers

24 dBm

## Electrical Specifications, Tx (Downlink)

### Operating Frequency Band

758 – 768 MHz (FirstNet) | 758 – 775 MHz | 851 – 869 MHz

# 7831851-0011

---

<b>Output Power @ One Carrier</b>	33 dBm
<b>Output Power @ Two Carriers</b>	30 dBm

## Environmental Specifications

<b>Operating Temperature</b>	-30 °C to +50 °C (-22 °F to +122 °F)
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP66   NEMA 4X   UL 2524 Certified   UL Type 4

## Packaging and Weights

<b>Weight, net</b>	19 kg   41.888 lb
--------------------	-------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

