

CMAX-DM60-43-153

Cell-Max™ Low PIM Directional High Capacity Venue MIMO Antenna, 698–960 MHz and 1710–2700 MHz, 60-Deg, 4.3-10

OBSOLETE

This product was discontinued on: April 15, 2018

Replaced By:

CMAX-DM60-43-V53 Cell-Max™ Low PIM Directional High Capacity Venue MIMO Antenna, 698–960 MHz and 1710–2700 MHz, 60°, 8.0 dBi

Product Classification

Product Type Indoor/outdoor antenna
Product Brand Cell-Max™

General Specifications


Application Indoor/Outdoor
Antenna Type Directional
Polarization ±45°
Color White
Number of Ports 2
Radome Material ABS, UV resistant
RF Connector Interface 4.3-10 Female

Dimensions

Width 299.7 mm | 11.799 in
Depth 124.5 mm | 4.902 in
Length 7,612.4 mm | 299.701 in

CMAX-DM60-43-153

Outline Drawing



Electrical Specifications

Impedance	50 ohm
Lightning Protection	dc Ground

Electrical Specifications

Frequency Band, MHz	698-800	800-960	1695-1880	1850-1990	1920-2180	2200-2700	2300-2360
Gain, dBi	8.5	9.2	9.3	9.6	9.8	9.2	8.9
Beamwidth, Horizontal, degrees	62	59	55	52	55	62	70
Beamwidth, Vertical, degrees	62	58	55	54	55	59	65
Front-to-Back Total Power at 180° ± 30°, dB	26	26	27	28	29	27	29
CPR at Boresight, dB	24	24	20	20	20	20	20
Isolation, Cross Polarization, dB	30	30	30	30	30	30	30
VSWR Return loss, dB	1.9 10.1	1.9 10.1	1.8 10.9	1.8 10.9	1.8 10.9	1.8 10.9	1.8 10.9
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153	-153
Input Power per Port, maximum, watts	200	200	200	200	200	200	200

Mechanical Specifications

Wind Loading @ Velocity, maximum	294.0 N @ 216 km/h (66.1 lbf @ 216 km/h)
Wind Speed, maximum	216 km/h 134.216 mph

CMAX-DM60-43-153

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65
Vibration Test Method	ASTM D4169 IEC 60068-2-6

Packaging and Weights

Width, packed	350 mm 13.78 in
Depth, packed	230 mm 9.055 in
Length, packed	520 mm 20.472 in
Included	Mounting bracket
Packaging quantity	1
Weight, gross	7.7 kg 16.976 lb
Weight, net	2.9 kg 6.393 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

