

Rollable ribbon OSP fiber cable portfolio



With the new rollable ribbon fiber cable portfolio, CommScope offers one of the industry's most innovative technologies specially designed to solve today's challenging needs for increased density and reduced footprint in applications ranging from data centers to FTTX distribution hubs and access network closures and terminals.

The rollable ribbon fiber cable portfolio meets the most rigorous optical and mechanical industry standards for outside plant fiber optic cables, ensuring reliable performance regardless of the environmental conditions or placement in confined and tight spaces.


In addition, a completely gel-free design helps reduce the time required to prepare for splicing, therefore reducing labor costs.

Features and benefits


- · Ultra-high fiber density with reduced footprint and weight
- 2X fiber density (more fiber and less space) versus flat ribbon designs
- · Reduced weight by 35% or more
- Rollable ribbon cable with standard loose tube series is available in 432, 576, 864, and 1728 fiber counts
- Rollable ribbon cable with central tube series is available in 144, 288 and 432 fiber counts
- Standard ribbon print marking with blocks and bars for ease of identification
- · Optimized for fast, cost-effective mass splicing
- Reduced splicing prep time by up to 80% (over traditional gel-filled ribbon cable designs)
- · Completely gel-free design
- Meets GR-20 Issue 4 and ANSI/ICEA S-87-640

Description

The rollable ribbon cable design is based on individual 250 µm fibers that are partially bonded to each other at predetermined points. Smaller distances between fiber attachment locations provides flatter, more controllable ribbons during splicing versus other collapsible ribbon designs. Color coded buffer tubes and numbered, striped ribbons are more easily identified. G.657.A1 fiber provides excellent bending performance with seamless splicing to the installed base of fibers.




Standard loose tube series





Rollable ribbon fiber cable central tube series





Rollable ribbon fiber cable

Rollable ribbon fiber cable central tube series

Performance and environmental specifications

Specifications											
				Dielectric	versions				Armored	lversions	
Fiber Count		96	144	288	432	864	96	144	288	432	864
Cable outer diamet	er – in. (mm)	.50 (12.6)	.50 (12.6)	.55 (13.9)	.65 (16.5)	.78 (19.8)	.47 (12.0)	.47 (12.0)	.55 (14.0)	.64 (16.3)	.81 (20.6)
Cable weight – lb/k	ft (kg/km)	71 (106)	71 (106)	101 (150)	126 (186)	163 (243)	107 (159)	107 (159)	137 (204)	157 (234)	228 (340)
Handling (all fiber counts)											
Maximum bend radius, with load		15 x OD (outer diameter)									
Maximum bend rad no load	lius, with	15 x OD									
Maximum bend rad coils	lius, storage	15 x OD									
Maximum rated cable load (MRCL)		600 lb. (2700 N)									
Maximum long-term load		180 lb. (800 N)									
Temperature	Installation	-22 to 140 °F (-30 to 70 °C)									
	Operation	-40 to 158 °F (-40 to 70 °C)									
	Storage	-40 to 167 °F (-40 to 75 °C)									
Performance stand	ards (all fiber	counts)									
Tested per applicable requirements of ANSI/ICEA-S-87-640 and Telcordia GR-20 CORE Issue 4.											





Rollable ribbon fiber cable central tube dielectric

Dry Core Rollable Ribbon Cable with Metalic Sheath



central tube armored

Rollable ribbon fiber cable central tube series

Performance and environmental specifications

Specifications								
		Dielectric	versions	Armored	l versions			
Fiber Count		144	288	144	288			
Cable outer diameter	– in. (mm)	0.39 (10)	0.47 (12)	0.57 (14.5)	0.65 (16.5)			
Cable weight – lb/kft	(kg/km)	55 (82)	77 (115)	127 (189)	163 (243)			
Handling (all fiber co	unts)							
Maximum bend radiu	s, with load	15 x OD (outer diamete	r)					
Maximum bend radius, with no load		15 x OD	15 x OD					
Maximum bend radius, storage coils		15 x OD	15 x OD					
Maximum rated cable load (MRCL)		600 lb. (2700 N)	600 lb. (2700 N)					
Maximum long-term load		180 lb. (800 N)	180 lb. (800 N)					
Installation		-22 to 140 °F (-30 to 7	-22 to 140 °F (-30 to 70 °C)					
Temperature	Operation	-40 to 158 °F (-40 to 7	0 °C)					
	Storage	-40 to 167 °F (-40 to 7	5 °C)					
Performance standard	ds (all fiber counts)							
Tested per applicable	requirements of ANSI/ICEA	-S-87-640 and Telcordia GR-2	0 CORE Issue 4.					

Rollable ribbon fiber cable Rollable ribbon fiber cable central tube dielectric central tube armored Outer Jacket Outer Jacket Strength Elements Corrugated Armor Water-Blocking Tape Strength Elements Ripcord Inner Jacket Central Tube Water-Blocking Tape Water-blocking Tape Central Tube 12-Fiber Rollable Ribbons Water-blocking Tape 12-Fiber Rollable Ribbons Ripcord


Rollable ribbon fiber cable standard loose tube series


Performance and environmental specifications


Application					
Dielectric construction					
Fiber count	432	576-864	1728		
Number of fibers per tube	72	144	288		
Cable outer diameter – in. (mm)	0.66 (16.8)	0.82 (21)	0.99 (25.1)		
Cable Weight – lb/kft (kg/km)	141 (210)	212 (315)	310 (460)		
Buffer tube diameter – in. (mm)	0.18 (4.5)	0.24 (6.0)	0.28 (7.0)		
Recommended duct size	1 in.	1 in.	1 1/4 in.		
Metallic construction					
Fiber count	432	576-864	1728		
Number of fibers per tube	72	144	288		
Cable outer diameter – in. (mm)	0.73 (18.6)	0.82 (23.2)	1.05 (26.8)		
Cable Weight – lb/kft (kg/km)	195 (290)	281 (418)	366 (545)		
Buffer tube diameter – in. (mm)	0.18 (4.5)	0.24 (6.0)	0.30 (7.0)		
Recommended duct size	1 in.	1 in.	1 1/4 in.		
Handling (all fiber counts)					
Minimum bend radius, with load	15 x OD (outer o	diameter)			
Minimum bend radius, with no load	15 x OD				
Minimum bend radius, storage coils	15 x OD				
Rated installation load	1000 lb. (4448 N	۷)			
Maximum long-term load	333 lb. (1481 N)				
Performance standards (all fiber counts)					
Tested per applicable requireme Telcordia GR-20 CORE Issue 4.	ents of ANSI/ICE	A-S-87-640 and			
Temperature (all fiber counts)					
Installation	-22 to 140 °F (-3	30 to 60 °C)			
Operation	-40 to 158 °F (-4	10 to 70 °C)			
Storage	-40 to 167 °F (-4	10 to 75 °C)			

Number of Fibers per tube

432	576-864	1728
72	144	288







Ordering information

ribbon fiber cable portfo	olio			
Fiber Count	Central tube			
riber Count	Non-armored	Armored		
96	D-096-CN-RR-F12NS/8W/99A	D-096-CA-RR-F12NS/8W/99A		
144	D-144-CN-RR-F12NS/8W/99A	D-144-CA-RR-F12NS/8W/99A		
288	D-288-CN-RR-F12NS/8W/99A	D-288-CA-RR-F12NS/8W/99A		
432	D-432-CN-RR-F12NS/8W/99A	D-432-CA-RR-F12NS/8W/99A		
864	D-864-CN-RR-F12NS/8W/99A	D-864-CA-RR-F12NS/8W/99A		
Fiber Count	Central tube			
riber Count	Non-armored	Armored, double jacket		
144	D-144-CN-RR-F12NS/8W/99G	D-144-C2-RR-F12NS/8W/99J		
288	D-288-CN-RR-F12NS/8W/99G	D-288-C2-RR-F12NS/8W/99J		
Fiber Count	Stranded Loose Tube			
riber Count	Non-armored	Armored		
432	D-432-LN-RR-F12NS/8W/99H	D-144-LA-RR-F12NS/8W/99H		
576	D-576-LN-RR-F12NS/8W/99H	D-576-LA-RR-F12NS/8W/99H		
864	D-864-LN-RR-F12NS/8W/99H	D-864-LA-RR-F12NS/8W/99H		
1152	D-1152-LN-RR-F12NS/8W/99H	D-1152-LA-RR-F12NS/8W/99H		
1440	D-1440-LN-RR-F12NS/8W/99H	D-1440-LA-RR-F12NS/8W/99H		
1728	D-1728-LN-RR-F12NS/8W/99H	D-1728-LA-RR-F12NS/8W/99H		

CommScope E-Catalog CLICK HERE. Additional product information, installation instructions and videos are available.

CommScope pushes the boundaries of communications technology with game-changing ideas and ground-breaking discoveries that spark profound human achievement. We collaborate with our customers and partners to design, create and build the world's most advanced networks. It is our passion and commitment to identify the next opportunity and realize a better tomorrow. Discover more at commscope.com

COMMSCOPE®

commscope.com

Visit our website or contact your local CommScope representative for more information.

© 2021 CommScope, Inc. All rights reserved.

Unless otherwise noted, all trademarks identified by @ or TM are registered trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services. CommScope is committed to the highest standards of business integrity and environmental sustainability with a number of CommScope's facilities across the globe certified in accordance with international standards, including ISO 9001, TL 9000, and ISO 14001.

Further information regarding CommScope's commitment can be found at www.commscope.com/About-Us/Corporate-Responsibility-and-Sustainability.