



Public Safety BDA for 700 AND 800 MHZ 2W CLASS B DC

- Compact, high-performance, economical public safety signal source
- UL2524 Certified – UL File S36319
- High performance architecture that supports up to 3 wide band filters
- Automatic Gain Control (AGC) and channelized uplink squelch ensure clear voice transmission
- Output power and band capacity can be field-upgraded via license key
- Web-based GUI and SNMP support for intelligent configuration and monitoring
- NFPA 1221 and IFC compliant
- Automatic oscillation detection and self-healing mechanism
- Built-in automatic donor antenna supervision
- Short installation time due to built-in isolation test, alarm test and one click summary report

Product Classification

Product Type Public safety RF repeater unit

General Specifications

Antenna Interface at Repeater 4.3-10

Indoor Antenna Optional, not included

Performance Note Values typical, unless otherwise stated

Supervision/Control Option Dry alarm contacts with 2.2k Ohm EOL resistors | Remote control via Ethernet

Dimensions


Height 480 mm | 18.898 in

Width 400 mm | 15.748 in

Depth 170 mm | 6.693 in

Optional Antenna Length 90 mm | 3.543 in

Outline Drawing



Electrical Specifications

Electrical Safety Standard

CAN/CSA-C22.2 No. 62368-1 | UL 2524 Certified | UL 62368 | US FCC Part 20 | US FCC Part 90

Gain, typical

90 dB

Gain Adjustment Range

30 dB

License Band

700 (including FirstNet) | 800

Local Power

-48 Vdc

Return Loss

13 dB

Power Consumption

160 W

Electrical Specifications, Rx (Uplink)

Operating Frequency Band

788 – 798 MHz (FirstNet) | 788 – 805 MHz | 796 – 824 MHz

Output Power @ One Carrier

27 dBm

Output Power @ Two Carriers

24 dBm

Electrical Specifications, Tx (Downlink)

Operating Frequency Band

758 – 768 MHz (FirstNet) | 758 – 775 MHz | 851 – 869 MHz

Output Power @ One Carrier

33 dBm

7831851-0021

Output Power @ Two Carriers 30 dBm

Environmental Specifications

Operating Temperature -30 °C to +50 °C (-22 °F to +122 °F)

Ingress Protection Test Method IEC 60529:2001, IP66 | NEMA 4X

Packaging and Weights

Weight, net 19 kg | 41.888 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

