


E20-2" SDR13.5-715JCASS-12.7MB

E20® Coaxial/Microduct Hybrid Buried Cable



- E20 is a solution that enables service providers the ability to bridge HFC networks to FTTx. The E20 composite coaxial/fiber product line combines fiber, microducts, and coaxial cable preinstalled in conduit
- Serves businesses in a new commercial serving area
- Mitigates future cost of fiber installation
- Pre-installed in high density PE conduit for added physical protection
- One-step installation saves on construction cost
- Ideal for commercial data customers that also require video
- All products tested to industry standards

OBSOLETE

Product Classification

Product Type	Coaxial fiber cable-in-conduit
Product Brand	E20®

General Specifications

Cable Series	QR 715
---------------------	--------

Dimensions

Height	60.325 mm 2.375 in
Width	60.325 mm 2.375 in
Outer Jacket Thickness, nominal	4.724 mm 0.186 in

Material Specifications

Outer Jacket Material	High density polyethylene (HDPE)
------------------------------	----------------------------------

Mechanical Specifications

Minimum Bend Radius	660.4 mm 26 in
Pulling Tension, maximum	1,170.268 kg 2580 lb

Environmental Specifications

Environmental Space	Buried
----------------------------	--------

E20-2" SDR13.5-715JCASS-12.7MB

Packaging and Weights

Weight, gross 1,142.91 kg/km | 768 lb/kft

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

- 360000000
12.7MB DUCT EMPTY – ConQuest® Empty Conduit, 12.7 mm, black
- 360000013
12.7MB DUCT EMPTY – ConQuest® Empty Conduit, 12.7 mm, black
- 5513592
QR® 715 JCASS – 75 Ohm QR® Trunk and Distribution Cable, black PE jacket, flooded for underground
- CX3799839
200T135 EMPTY DUCT COEX – ConQuest® Empty Conduit, 2 in, SDR 13.5, terracotta