

# CSV8GD-1.8

## HomeConnect® Eight-way Splitter, 5–1218/1800 MHz, Dual Mount



**OBSOLETE**

### Product Classification

<b>Product Type</b>	Coaxial splitter
<b>Product Brand</b>	HomeConnect®

### General Specifications

<b>Device Type</b>	Splitter
<b>Application</b>	Indoor   Outdoor
<b>Mounting</b>	Horizontal   Vertical
<b>Video Ports, quantity</b>	8

### Electrical Specifications

<b>Insertion Loss at Frequency Band, typical</b>	10.5 dB @ 5–400 MHz   13.0 dB @ 400–1218 MHz   15.0 dB @ 1218–1800 MHz
<b>Return Loss at Frequency Band, input, minimum</b>	16 dB @ 1218–1800 MHz   18 dB @ 1002–1218 MHz   20 dB @ 5–1002 MHz
<b>Return Loss at Frequency Band, output, minimum</b>	16 dB @ 1218–1800 MHz   18 dB @ 1002–1218 MHz   20 dB @ 5–1002 MHz
<b>Frequency Response</b>	±0.5 dB @ 1002–1800 MHz   ±0.5 dB @ 5–1002 MHz
<b>Impedance</b>	75 ohm
<b>Operating Frequency Band</b>	5 – 1800 MHz
<b>Power Passing</b>	No
<b>Shielding Effectiveness, minimum</b>	120 dB
<b>Spurious Signals/2nd Order Harmonics, before surge</b>	<-100 dBc

# CSV8GD-1.8

---

## Surge Capability Test Method

ANSI/SCTE 81 | Category A3 (6 kV, 200 A, Ring wave)

## Surge Capability Waveform

100 kHz ring wave waveform

## Electrical Specifications, Isolation

### Isolation at Frequency Band, output to output, minimum

18 dB @ 1218–1800 MHz | 20 dB @ 1002–1218 MHz | 22 dB @ 5–10 MHz | 22 dB @ 870–1002 MHz | 26 dB @ 65–870 MHz | 30 dB @ 10–65 MHz

## Environmental Specifications

### Operating Temperature

-40 °C to +60 °C (-40 °F to +140 °F)

### Grounding and Bonding Standard

UL 467 Ground Clamp Communication

### Safety Standard

SCTE

## Packaging and Weights

### Height, packed

215 mm | 8.465 in

### Width, packed

370 mm | 14.567 in

### Length, packed

495 mm | 19.488 in

### Carton Quantity

120

### Weight, gross

22.6 kg | 49.824 lb

## Regulatory Compliance/Certifications

### Agency

CE

### Classification

Compliant with the relevant CE product directives

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

