






ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT
1	EQ-P6C041401	14' Platform Channel Side	2	116.49 LBS
2	EQP6C040801	4' Platform Channel Center	5	29.80 LBS
3	EQP041401	Grating Section Bracket 4' Wide Platform	1	20.62 LBS
4	MTC79020407.03	24" X 84" BAR GRATING	4	99.01 LBS
5	MTCP.01	6" Channel Adapter Angle	10	3.18 LBS
6	GB-05205	5/8" X 2" GALV BOLT KIT	42	0.27 LBS
7	GWF-05	5/8" GALV FLAT WASHER	84	0.06 LBS
8	GCM03	GRATING CLIP	24	0.39 LBS

REVISIONS				
REV.	ZONE	DESCRIPTION	BY	DATE
A		INITIAL RELEASE	DRR	03/17/11
B		REVISED BILL OF MATERIALS	DRR	05/15/12




DETAIL A  
SCALE 1 : 11



NOTES:

- ALL METRIC DIMENSIONS ARE IN BRACKETS.
- STAMP PART IDENTIFICATION NUMBER.
- GRATING REMOVED FOR CLARITY.

<small>These drawings and specifications are the proprietary property of ANDREW CORPORATION and may be used only for the specific purpose authorized in writing by Andrew Corporation.</small> ALL DIMENSIONS ARE IN INCHES U.O.S. TOLERANCES UNLESS OTHERWISE SPECIFIED: .X = ± .12      ANGLES      ±2° .XX = ± .06      FRACTIONS      ±1/32 .XXX = ± .031 REMOVE BURRS AND BREAK EDGES .005 DO NOT SCALE THIS PRINT	DRAWN BY: <b>DRR</b>	SHEET: 1 of 1	PART NUMBER: <b>EQ-P6C0414-B</b>
	CHECKED BY: <b>TP</b>	SCALE: NTS	DESCRIPTION: 4' X 14' Equipment Platform
	DATE: 03/17/11	MATERIAL: A36, A568	DRAWING TYPE: ASSEMBLY SHOP DRAWING
	REVISION: <b>B</b>	FINISH: GALV A123	 WESTCHESTER, IL. 60154 U.S.A.
	WEIGHT: 860.27 LBS		