

# **Installation Instructions**

TC-96203-IP Rev. A, April 2017 www.commscope.com

# Mini-OTE 300 Tap

#### Contents


1	General.	1
1.1	Adapter Options:	2
2	Mounting Options	2
3	Using Hardened Connectors and Adapters	
3.1	Connector Components	3
3.2	Drop Cable Connector Components	3
3.3	Connecting Drop Cable to Mini-OTE Optical Port	4
3.4	Disconnecting Drop Cable from Mini-OTE Optical Port	6
4	Maintenance of Mini-OTE 300 Terminals.	6
4.1	Drop Cable Connector Cleaning Procedure.	6
4.2	Mini-OTE Adapter/Connector Cleaning Procedure	
5	O-Ring Lubrication	
6	Product Support	. 10


#### General

The Mini-OTE 300 optical terminal enclosure is a unique plug-n-play solution for tap deployments in Fiber-To-The-x (FTTx) architectures. Featuring pre-connectorized hardened full-size OptiTap® or mini-size DLX® adapter ports, CommScope's Mini-OTE 300 accelerates fiber deployment for new subscriber activation and service, minimizing labor costs. Each terminal is delivered with the tap pre-installed in the terminal and all feeder and drop ports are sealed with a plug. The terminal housing is closed and secured to prevent damage to internal splices.

The unit is designed for installation in pedestal, hand hole, pole and strand mount applications. Accessory kits are available to provide hardware and brackets required for pole and strand installations. In some pedestal styles, the strand mount brackets can be used for terminal stability such as pedestals with a mounting stake or D-bar design. Once the field technician has secured the terminal housing using with the appropriate hardware, the Mini-OTE is ready for drops to be connected to the adapter ports. Each terminal has pre-defined port access to the Tap Input, Tap Thru and Splitter Outputs.

The Tap Input is color coded green and is Port position #3 (first row, second from right side) on all Tap models. The Tap Thru is color coded orange and is Port position #4 (first row, first port on right side of the terminal). Second and third rows on the 8 Port and 12 Port models are Splitter Outputs. See Figure 1.








Figure 1. Mini-OTE Tap Ports

#### 1.1 Adapter Options:

Adapter options include the following:

- 4 Port Mini-Size DLX
- 8 Port Mini-Size DLX
- 12 Port Mini-Size DLX
- 4 Port Full Size DLX
- 8 Port Full Size DLX
- 12 Port Full Size DLX

Table 1 summarizes the port locations and functions.

1x2 Tap 1x4 Tap 1x8 Tap Row (4 Port Terminal) (12 Port Terminal) (8 Port Terminal) 1 Port#1 N/A; Port#2 N/A; Port#1 & 2 Drop Outputs; Port#1 N/A; Port#2 N/A; Port#3 Tap Input; Port#3 Tap Input; Port#3 Tap Input; Port#4 Tap Thru Port#4 Tap Thru Port#4 Tap Thru 2 N/A Port#1 N/A; Port#2 N/A; Port#5 through Port#8: Port#3 Tap Input; Port#4 **Drop Outputs** Tap Thru 3 N/A N/A Port#9 through Port#12: **Drop Outputs** 

**Table 1: Mini-OTE Ports** 

# **2** Mounting Options

The OTE-M-STRAND-BRKT accessory kit provides two brackets and hardware for mounting the Mini-OTE 300 in strand mount applications and some pedestal applications depending on the pedestal design. Figure 2 shows the mounting options.








Figure 2. Mounting Options

The OTE-M-STRAND-CLAMP accessory kit provides two strand clamps and hardware for mounting the Mini-OTE 300 terminal closer to the D-Bar or to a universal back plate. This device is included in the Mini-OTE 300 kits. Figure 3 shows the strand mount clamps and hardware and the installation options.







Figure 3. Strand Mount Clamps/Hardware – Pedestal Installation Options

## 3 Using Hardened Connectors and Adapters

Hardened connectors and adapters provide sealed environmental protection for the subscriber drop cable connector and the SC adapter mounted within the Mini-OTE optical port. The following sections provide a description of the connector and adapter components and provide instructions for connecting or disconnecting the drop cable to/from the optical ports.

## 3.1 Connector Components

The basic components of the drop cable connector are shown in Figure 4. The dust cap threads onto the connector coupling nut. A pair of O-rings on the connector body provide a tight seal when the dust cap is in place. A pulling eye is provided in the end of the dust cap for pulling the drop cable through conduit.




Figure 4. Connector Components

### 3.2 Drop Cable Connector Components

The basic components of the Mini-OTE optical port hardened adapter are shown in Figure 5. The dust cap threads into the adapter housing. An O-ring on the dust cap provides a tight seal when the dust cap is in place. The 216B key tool is required to remove the dust cap.




Figure 5. Optical Port Components

## 3.3 Connecting Drop Cable to Mini-OTE Optical Port

**Danger!** Exposure to laser radiation can seriously damage the retina of the eye. Do not look into the ends of any optical fiber. Do not assume the laser power is turned-off or that the fiber is disconnected at the other end.

Use the following procedure to connect a drop cable to an optical port on the Mini-OTE enclosure:

- 1. Unscrew the dust cap from the drop cable connector (see Figure 4 on Page 3).
- 2. Inspect the drop cable connector O-rings for dryness and apply O-ring lubricant (MST-ACC-LUBE1) to each O-ring if dry. See Section 5 on page 9.

**Note:** The connector O-rings are pre-lubricated by the factory and should not require additional lubrication for the initial assembly.

- 3. Use the 216B key tool (accessory) to unscrew the dust cap (see Figure 5) from the Mini-OTE optical port.
- 4. Clean both the optical port adapter and the drop cable connector (requires accessory kit FHD-ACC-CLNKIT1) as specified in ADCP-96-067.
- 5. Align the drop cable connector with the optical port as shown in Figure 6. The pointer on the drop cable connector should line up with the notch on the optical port.
- 6. Insert the drop cable connector into the optical port. If the drop cable connector does not insert all the way to the bottom of the port, rotate drop cable connector slightly to either side until it slides freely into place.
- 7. Thread the drop cable connector coupling nut into the optical port and tighten coupling nut until finger tight.
- 8. Inspect the optical port dust cap O-ring (see Figure 4 on Page 3) for dryness and apply O-ring lubricant to the O-ring if dry (MST-ACC-LUBE1). For the procedure, refer to Section 5 on page 9.

**Note:** The optical port dust cap O-ring is pre-lubricated by the factory and should not require additional lubrication for the initial assembly.

Thread the optical port dust cap into the drop cable dust cap as shown in Figure 7 and then tighten both dust caps finger tight. This ensures that both dust caps will stay clean when not in use.




Figure 6. Connecting Drop Cable to Mini-OTE Optical Port




Figure 7. Dust Caps

## 3.4 Disconnecting Drop Cable from Mini-OTE Optical Port

#### Danger!

Exposure to laser radiation can seriously damage the retina of the eye. Do not look into the ends of any optical fiber. Do not assume the laser power is turned-off or that the fiber is disconnected at the other end.

Use the following procedure to disconnect a drop cable from an optical port on the Mini-OTE terminal:

- 1. Unscrew the optical port dust cap from the drop cable dust cap (see Figure 7).
- 2. Unscrew the drop cable connector coupling nut from the optical port (see Figure 6).
- 3. Inspect the optical port dust cap O-ring for dryness and apply O-ring lubricant (MST-ACC-LUBE1) to the O-ring if dry. For the procedure, refer to Section 5 on page 9.
- 4. Thread the optical port dust cap into the optical port and tighten using the 216B key tool (see Figure 5).
- 5. Inspect the drop cable connector O-rings for dryness and apply O-ring lubricant (MST-ACC-LUBE1) to each O-ring if dry. For the procedure, refer to Section 5 on page 9.
- 6. Thread the drop cable dust cap onto the drop cable connector coupling nut and tighten until finger tight (see Figure 4).

#### 4 Maintenance of Mini-OTE 300 Terminals

Maintenance for the Mini-OTE terminal is limited to cleaning the hardened adapters as needed to maintain optimal performance, lubricating O-rings that may become dry, or replacing a damaged optical connector.

### 4.1 Drop Cable Connector Cleaning Procedure

Cleaning kit (FHD-ACC-CLNKIT1) is required for this procedure. Use the following procedure to clean the drop cable connector:

Note: Use the approved local cleaning device that has slots for a hardened connector shroud.

- 1. Unscrew the drop cable connector dust cap from the end of the drop cable connector.
- 2. Examine the end of the drop cable connector and determine which is the high side and which is the low side of the connector end-face as shown in Figure 8.




Figure 8. Angled Connector End-Face Detail

- 3. Locate the cleaning tape cassette that is provided with the cleaning kit.
- 4. Open the tape shutter by squeezing the lever on the underside of the cassette and then keep the shutter open by continuing to squeeze the lever.
- 5. Hold the end-face of the drop cable connector perpendicular to the cleaning tape and with the high side of the connector pointing in the direction of cleaning as shown in Figure 9.

**Note:** The drop cable connector uses angled SC type connectors. Make sure the high side of the connector end-face is pointing in the direction of the cleaning motion.

6. With light pressure, slide the connector end-face once across the tape in the direction shown using a smooth linear motion. Do not press too hard and do not repeat the cleaning motion with the same tape.




Figure 9. Angled Connector End-Face Detail

- 7. Release the lever on the underside of the cassette to close the tape shutter.
- 8. Repeat steps 3 through 6 until the connector has been cleaned three times.
- 9. When the connector is clean, reinstall the drop cable dust cap and tighten until finger tight.

#### 4.2 Mini-OTE Adapter/Connector Cleaning Procedure

Cleaning kit (FHD-ACC-CLNKIT1) is required for this procedure. Use the following procedure to clean the Mini-OTE optical port adapters and the internal connectors:

- 1. Using a 216B key tool, unthread the optical port dust cap from the optical port adapter.
- 2. Locate the dry swabs that are provided with the connector/adapter cleaning kit.
- 3. Insert a dry swab into the adapter as shown in Figure 10.

**Note:** Do not apply alcohol to the swab or the adapter.

- While applying light pressure against the connector end-face, rotate the dry swab 360° three times
- 5. Dispose of the dry swab after use.
- 6. When the connector end-face and adapter ferrule are clean, reinstall the optical port dust cap and tighten using the 216B key tool.




Figure 10. Cleaning Optical Port Connecter and Adapter

## 5 O-Ring Lubrication

The O-rings used on the hardened connector and on the optical port dust cap are lubricated when shipped from the factory to prevent damage during installation.

If the O-rings become excessively dry, they may require additional lubrication to prevent damage. Remove the O-rings from the connector or dust cap and apply a small amount of lubricant directly to each ring. Then reinstall the O-rings on the connector or dust cap. Apply only the recommended O-ring lubricant (MST-ACC-LUBE1).

# **6** Product Support

- To find out more about CommScope® products, visit us on the web at www.commscope.com/
- For technical assistance, customer service, or to report any missing/damaged parts, visit us at <a href="http://www.commscope.com/SupportCenter">http://www.commscope.com/SupportCenter</a>

