



Toneable ConQuest® Empty Conduit, 2 in, SCH 40, terracotta, with pull tape

Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Terracotta
Conductor Elongation, maximum	30 %
Conductor Type	Solid
Conduit Type	Toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	762 m 2500 ft
Conductor Diameter	1.024 mm 0.04 in
Inner Diameter, nominal	51.994 mm 2.047 in
Outer Diameter, nominal	60.325 mm 2.375 in
Wall Thickness Designation	SCH 40
Wall Thickness, minimum	3.912 mm 0.154 in
Nominal Size	2 in
Conductor Gauge	18 AWG

3799107 | 200T(TD)040WP1800TAPE

Electrical Specifications

Conductor Resistance 98.425 ohms/km | 30 ohms/kft

Material Specifications

Conductor Material Type Copper-clad steel (CCS)
Flexural Modulus, minimum 551.581 N/mm² | 80000 psi
Flexural Property Test Method ASTM D790
Hydrostatic Design Basis Not pressure rated
Hydrostatic Design Test Method ASTM D2837
Material Type High density polyethylene (HDPE) | Polyester
Melt Flow Rate Test Method ASTM D1238
Melt Flow Rate, maximum 0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported 660.4 mm | 26 in
Tensile Property Test Method ASTM D638
Tensile Strength at yield, minimum 20.684 N/mm² | 3000 psi
Breaking Strength 816.466 kg | 1800 lb
Conductor Tensile Strength, minimum 344.738 N/mm² | 50000 psi
Pull Line Type Tape
Pulling Tension Note Applies to products manufactured after December 31, 2012
Pulling Tension, maximum 1,043.262 kg | 2300 lb

Environmental Specifications

Environmental Stress Crack Resistance Failure rate of 10% within 96 hours
Environmental Stress Test Method ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net 702.413 kg/km | 472 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance