

TNC Male for CNT-400 braided cable

Product Classification

 Product Type
 Braided cable connector

 Product Brand
 CNT® | ConQuest®

General Specifications

Body Style Straight
Inner Contact Attachment Method Captivated

Inner Contact Plating Gold

 Interface
 TNC Male

 Outer Contact Attachment Method
 Clamp

Outer Contact Plating Trimetal


Dimensions

 Length
 41.24 mm | 1.624 in

 Diameter
 18 mm | 0.709 in

Nominal Size 0.405 in

Outline Drawing



Electrical Specifications

0.05 dB Insertion Loss, typical **Cable Impedance** 50 ohm **Connector Impedance** 50 ohm dc Test Voltage 1500 V 1.5 mOhm Inner Contact Resistance, maximum Insulation Resistance, minimum 5000 MOhm **Operating Frequency Band** 0 - 6000 MHz **Outer Contact Resistance, maximum** 0.4 m0hm Peak Power, maximum 5 kW RF Operating Voltage, maximum (vrms) 500 V

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0-3000 MHz	1.046	32.96
3000-6000 MHz	1.18	22

Mechanical Specifications



Connector Retention Tensile Force 330 N | 74.187 lbf

Connector Retention Torque 0.56 N-m | 4.956 in lb

Coupling Nut Proof Torque 1.7 N-m | 15.046 in lb

Coupling Nut Proof Torque Method IEC 61169-17:9.3.6

Coupling Nut Retention Force 445 N | 100.04 lbf

Coupling Nut Retention Force Method IEC 61169-17:9.3.11

Interface Durability 500 cycles

Interface Durability Method IEC 61169-17:9.5

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ $(-40 \,^{\circ}\text{F to} +185 \,^{\circ}\text{F})$

Storage Temperature -65 °C to +125 °C (-85 °F to +257 °F)

Attenuation, Ambient Temperature 20 °C | 68 °F

Average Power, Ambient Temperature 40 °C | 104 °F

Average Power, Inner Conductor Temperature 100 °C | 212 °F

Climatic Sequence Test Method IEC 60068-1

Corrosion Test Method IEC 60068-2-11

Damp Heat Steady State Test Method IEC 60068-2-3

Immersion Depth 1 m

Immersion Test Mating Mated

Immersion Test Method IEC 60529:2001, IP68

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Weight, net 41.85 g | 0.092 lb

Regulatory Compliance/Certifications

Agency	Classification	

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

COMMSCOPE®

ROHS

Compliant

UK-ROHS

Compliant





* Footnotes

Insertion Loss, typical 0.05√ freq (GHz) (not applicable for elliptical waveguide)

Immersion Depth Immersion at specified depth for 24 hours

