

ICX7550-48F | RUCKUS ICX 7550-48F



Entry-Level Aggregation 48 Ports 1G/10G SFP/SFP+ Switch

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Ethernet switch
Product Brand	RUCKUS®

General Specifications

Switching Capacity, maximum	912 Gb/s
1 GbE SFP Ports, quantity, maximum	48
10 GbE SFP+ Ports, quantity, maximum	12
40 GbE QSFP Ports, quantity, maximum	4
100 GbE QSFP28 Ports, quantity, maximum	2
Switches per Stack, maximum	12
Aggregate Stack Bandwidth, maximum	2400 Gb/s
PoE/PoE+	No
Stacking	Yes
sFlow	Yes
Layer 3 (STATIC, RIP, OSPF)	Yes
OpenFlow with Hybrid Port Mode	Yes
Campus Fabric Technology	No
Redundant Power Option	Yes
Hot Swap Internal Power Supplies & Fans	Yes
802.3bt2 (90 W PoE Power per Port)	No
VRF	Yes
EEE (Energy Efficient Ethernet)	Yes
IPsec VPN, with service module	No
MACsec	Yes
BGP	Yes

ICX7550-48F | RUCKUS ICX 7550-48F

Reversible Airflow Option	Yes
VxLAN	Yes

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

