


760250640 | FT 2MM PVC SP 1050X1400UM PVDF AQ



Furcation Tubing for Optical Fiber, indoor, PVC jacket, PVDF tubing, 1.4/2.0 mm, with strength member, aqua

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America
Product Type Furcation tubing

General Specifications

Application For use with all fiber connector types | For use with singlemode and multimode optical fibers
Color Aqua

Dimensions

Length 1000 m | 3,280.84 ft
Inner Diameter, nominal 1.05 mm | 0.041 in
Outer Diameter, nominal 2.06 mm | 0.081 in

Material Specifications

Material Type PVC | PVDF

Mechanical Specifications

Minimum Bend Radius, Installation 3 mm | 0.118 in
Minimum Bend Radius, Long Term 5 mm | 0.197 in
Shrinkage, maximum 5 %

Environmental Specifications

Installation temperature 0 °C to +70 °C (-32 °F to +158 °F)
Operating Temperature -20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space Indoor

760250640 | FT 2MM PVC SP 1050X1400UM PVDF AQ

Packaging and Weights

Included	Aramid strength members
Packaging quantity	1
Packaging Type	Reel
Weight, net	3 kg/km 2.016 lb/kft

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable