

EG6120-000 | OCC1C-F-471-NNSEC



OCC1C compact CWDM, 8 channels + 1310 nm port, single demux, 1471 nm starting wavelength, 0.9 mm cable

OBSOLETE

This product was discontinued on: July 25, 2023

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	CWDM component
Product Series	OCC1C

General Specifications

Device Type	Component, rectangular
Functionality	Demultiplexing
Technology Type	Free space optics
Application	For use in FOXC closures
Circuits, quantity	1
Distribution Type	8-channel CWDM
Interface, Input	Stub tail
Interface, Output	Stub tail
Multiplexers, quantity	1
Port Type, optional	1310 nm port

Dimensions

Pigtail Length, Input	2.5 m 8.202 ft
Pigtail Length, Output	2.5 m 8.202 ft
Pigtail Diameter	0.9 mm 0.035 in

Optical Specifications

Channel Spacing	20 nm
Starting Wavelength	1471 nm

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

