


NGFB-TB5SRUK0BDXXX



Next Generation Frame (NGF) Fiber Termination Block with IFC Cable, Dual Rated, Rollable Ribbon singlemode, 288 LC/UPC to Stub tail, left oriented, upward cable exit, black

1-100 meters. For additional length options, contact your CommScope representative.

Product Classification

Regional Availability	Asia EMEA Latin America North America
Product Type	Fiber patch block, with IFC cable
Product Series	NGFB

General Specifications

Functionality	Patching
Application	Used with NGF-style frames only
Body Style	Left orientation
Cable Exit Location	Upward
Cable Type	IFC, rollable ribbon
Color	Black
Door Type, front	Compression latch Hinged
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Interface, rear	Stub tail
Rack Type	NGF
Shelf Movement	Sliding
Total Ports, quantity	288

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

NGFB-TB5SRUK0BDXXX

Fiber Mode	Singlemode
Fiber Type	G.657.A2 OS2

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 80%, non-condensing
Qualification Standards	Telcordia GR-449-CORE

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted



Included Products

760239308 N-288-CN-RR-F12YL/8G1/99G /C	-	Indoor, All-Dielectric, Low Smoke Zero Halogen (LSZH), Riser-Rated, Gel-Free, Central Tube Rollable Ribbon Cable
760245230 N-192-CN-RR-F12YL/8G1/99G /C	-	Indoor, All-Dielectric, Low Smoke Zero Halogen (LSZH), Riser-Rated, Gel-Free, Central Tube Rollable Ribbon Cable