

760243135 | FT 2MM PUR SP 440X920UM HYT -40 LF GR



Furcation Tubing for Optical Fiber, indoor, polyurethane jacket, TPE tubing, 0.44/2.0 mm, with strength member, green

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification
- Low shrinkage and superior resistance to chemicals and temperature

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Furcation tubing

General Specifications

Application

For use with all fiber connector types | For use with singlemode and multimode optical fibers

Color

Green

Dimensions

Length

1000 m | 3,280.84 ft


Inner Diameter, nominal

0.44 mm | 0.017 in

Outer Diameter, nominal

2 mm | 0.079 in

Outline Drawing



Material Specifications

Material Type Elastomer | Polyurethane | Thermoplastic polyester

Mechanical Specifications

Minimum Bend Radius, Installation 3 mm | 0.118 in

Minimum Bend Radius, Long Term 5 mm | 0.197 in

Shrinkage, maximum 5 %

Environmental Specifications

Installation temperature 0 °C to +60 °C (-32 °F to +140 °F)

Operating Temperature -20 °C to +75 °C (-4 °F to +167 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Indoor

Packaging and Weights

Included Aramid strength members

Packaging quantity 1

Packaging Type Reel

Weight, net 2.8 kg/km | 1.882 lb/kft

760243135 | FT 2MM PUR SP 440X920UM HYT -40 LF GR

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable