


# FD21204-48SRC-450



HELIAX® Pendant HCS 2.0; 6 x 24 hybrid cable includes 12-4AWG conductors x 48-single mode fibers. Top breakout (Pendant); 12 HQLC connectors with fiber and power outputs. Bottom breakout (BBU); blunt cut conductors and DLC connectors, 450 ft

- Note: 4AWG DC conductors are utilized for cable lengths 250 to 450 feet. 6AWG DC conductors are utilized for cable lengths 25 to 225 feet in the FD21206-48SRC-x product family

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Hybrid cable assembly
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	FD2

## General Specifications

<b>Conductors, quantity</b>	12
<b>Construction Type</b>	Direct breakout trunk
<b>Interface, Connector A</b>	HQ-LC
<b>Interface Feature, connector A</b>	Outdoor
<b>Interface Body Style, connector A</b>	Straight
<b>Interface, Connector B</b>	DLC
<b>Interface Feature, connector B</b>	Standard
<b>Interface Body Style, connector B</b>	Straight
<b>Total Fibers, quantity</b>	48

## Dimensions

<b>Cord Length</b>	129.74 m   425.656 ft
<b>Diameter Over Jacket</b>	44.7 mm   1.76 in
<b>Center Conductor Gauge</b>	4 AWG
<b>Center Conductor Gauge Note</b>	4 AWG DC conductors for cable lengths from 250 to 450 feet

## Mechanical Specifications

# FD21204-48SRC-450

---

**Minimum Bend Radius** 360.7 mm | 14.201 in

## Optical Specifications

**Fiber Type** G.657.A2/B2

**Assembly Insertion Loss, typical** 0.75 dB

**Assembly Insertion Loss, typical note** Insertion loss is measured at 1310 and 1550 nm

## Environmental Specifications

**Operating Temperature** -40 °C to +80 °C (-40 °F to +176 °F)

## Packaging and Weights

**Cable weight** 3.57 kg/m | 2.399 lb/ft

## \* Footnotes

**Assembly Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)