

# DHK-78-6-P



Double Hanger Kit for 7/8 in coaxial cable, triple stack; includes hardware and angle adapter

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	ValuSite™
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cables per Hanger</b>	6
<b>Color</b>	Black
<b>Hanger Type</b>	Composite clamp
<b>Harmonized System (HS) Code</b>	85366910 (Coaxial cable and other coaxial electric conductors)
<b>Mounting</b>	M8 hardware

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	20.8 mm   0.819 in
<b>Width</b>	26.2 mm   1.031 in
<b>Length</b>	37.6 mm   1.48 in
<b>Compatible Cable Diameter Range</b>	27.7–28.2 mm
<b>Compatible Diameter, maximum</b>	28.2 mm   1.11 in
<b>Compatible Diameter, minimum</b>	27.5 mm   1.083 in
<b>Nominal Size</b>	7/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic   Stainless steel
----------------------	--------------------------------------

# DHK-78-6-P

---

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 20.3 cm | 7.992 in

**Length, packed** 15.2 cm | 5.984 in

**Included** Angle adapter | Hardware

**Packaging quantity** 1

**Weight, gross** 0.27 kg | 0.595 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

ANGLE ADAPTER – Angle Adapter

HARDWARE – Hardware

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power

# ANGLE ADAPTER

---



Angle Adapter

## Product Classification

<b>Product Type</b>	Adapter
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Adapter Type</b>	Angle adapter
---------------------	---------------

## Dimensions

<b>Inside Width</b>	16.002 mm   0.63 in
<b>Inside Length</b>	16.002 mm   0.63 in
<b>Material Thickness</b>	2.972 mm   0.117 in

## Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

## Mechanical Specifications

<b>Installation Torque, maximum</b>	13 ft lb   17.626 N-m
<b>Installation Torque, minimum</b>	11 ft lb   14.914 N-m

# HARDWARE

---



Hardware

## Product Classification

**Product Type** Hardware kit

## General Specifications

**Thread Size** M8

## Dimensions

**Length** 170.18 mm | 6.7 in

## Environmental Specifications

**Corrosion Resistance, minimum with no degradation**  $\geq 500$  hours in salt spray chamber

## Packaging and Weights

**Included** Flat washers | Hex nuts | Lock washers | Threaded rod