

FA-17MM-114-AD



1 1/4 in Double Hanger Kit for HELIAX® Direct Power tails, 17 mm grommet, angle adapter, triple stack, kit of 10

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	6
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	3
Height	184.4 mm 7.26 in
Width	28.7 mm 1.13 in
Length	120.4 mm 4.74 in
Compatible Cable Diameter Range	16–17 mm
Compatible Diameter, maximum	17 mm 0.669 in
Compatible Diameter, minimum	16 mm 0.63 in

Material Specifications

Material Type	Corrosion proof coated metal Engineered plastic
----------------------	---

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
---------------------------	--------------------------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

FA-17MM-114-AD

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Packaging quantity	10
---------------------------	----

Included Products

- DHK-114-6-P – Double Hanger Kit for 1-1/4 in coaxial cable, triple stack; includes hardware and angle adapter
- HG-58-114 – Grommet with 19mm hole for 1-1/4 in SnapStak or polymer block hanger

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power