





ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT
1	WTMMP31	Monopole Weldment, 10ft	1	1148.15 LBS
2	WTMMP.22	3 PORT COVER	1	26.15 LBS
3	WTMMP.19	DBI/SALA SAFETY CLIMB KIT	1	
4	WTSPM.38	1" TAPERED PLUG 1" EXTERNAL THREAD	1	0.20 LBS
5	GB-0524A	5/8" X 2-1/2" GALV BOLT KIT (A325)	24	0.31 LBS
6	GB-04145	1/2" X 1-1/2" GALV BOLT KIT	3	0.31 LBS
7	GWF-04	1/2" GALV FLAT WASHER	3	0.01 LBS
8	EPCAP4.01	ENTRY PORT COVER 4"	9	0.10 LBS
9	MT75001	STEP BOLT	6	0.88 LBS


REVISIONS				
REV.	ZONE	DESCRIPTION	BY	DATE
A		INITIAL RELEASE	MSM	02/11/10
B		EPCAP4.01 WAS EPCAP4B.01	DRR	03/01/11



NOTES:
1. ALL METRIC DIMENSIONS ARE IN BRACKETS.



DETAIL A
SCALE 1 : 6

These drawings and specifications are the proprietary property of ANDREW CORPORATION and may be used only for the specific purpose authorized in writing by Andrew Corporation. ALL DIMENSIONS ARE IN INCHES U.O.S. TOLERANCES UNLESS OTHERWISE SPECIFIED: .X = ± .12 ANGLES ±2' .XX = ± .06 FRACTIONS ±1/32 .XXX= ± .03 REMOVE BURRS AND BREAK EDGES .005 DO NOT SCALE THIS PRINT	DRAWN BY: MSM	SHEET: 1 of 1	PART NUMBER: WT-MMP-10
	CHECKED BY: TP	SCALE: NTS	DESCRIPTION: 10' Mini Monopole
	DATE: 02/11/10	MATERIAL: A36, A53	DRAWING TYPE: ASSEMBLY DRAWING
	REVISION: B	FINISH: GALV A123 WEIGHT: 1188.51 LBS	 WESTCHESTER, IL. 60154 U.S.A.