



# C4<sup>®</sup> and C4c<sup>™</sup> CMTS 24 Upstream Cable Access Module (24U CAM) Technical Specifications

## Specifications

### RF Upstream

Frequency Range (MHz)	5 to 85 (5 to 65 with Software Release 8.0)
Modulation	QPSK, 8 QAM, 16 QAM, 32 QAM, 64 QAM
Channel Type	TDMA, ATDMA, TDMA/ATDMA, SCDMA
Data Rate (Mbps) (Max.)	30.72 per channel
RF Input Level (dBmV)	-16 to +29
Frequency Resolution (KHz)	< 1
Symbol Rate (Ksym/sec)	160, 320, 640, 1280, 2560, 5120
Bandwidth per Channel (MHz)	0.2, 0.4, 0.8, 1.6, 3.2, 6.4

### Physical

Power	-48 VDC (-44 to -72 VDC)
Power Consumption	100 W nominal and 125 W max at -48 VDC, 77°F (25°C)
Operating Temperature:	
Short Term °F (°C)	+23 to +131 (-5 to +55)
Long Term °F (°C)	+41 to +104 (+5 to +40)
Storage Temperature °F (°C)	-40 to +158 (-40 to +70)
Operating Humidity (Min.-Max.)	5 to 85% (Non condensing)
Dimensions (H x W x D) in. (cm)	15.8 x 0.8 x 15.0 (40.0 x 1.9 x 38.1)
Weight lbs. (kg)	approx 4 (1.8)

### Support with Software Release 8.0 (Partial Feature List)

24U CAM	BSoD L2 VPN
Flexible Mapping of Upstream Channels to F Connectors	BPI+ Enforce
Up to 12 Upstream Channels per F Connector	IPDR/SP
8 F Connectors per Physical Interface Card (PIC)	Integrated Upstream Agility
Up to 9+1 RF Sparing	PIM-SSM, IGMPv2, and static multicast
BPI/BPI+ Support	RIPv2 (RFC 1723), OSPFv2 (RFC 2328)
DOCSIS <sup>®</sup> 3.0 Multicast IP Video Support	Policy-Based Routing
IGMPv3 Control and CAC	PacketCable <sup>™</sup> Multimedia Support
IS-IS (including Multi-topology (MT)), BGPv4	Additional Classifier Support (for MGPI applications)
TFTP Enforce and Dynamic MIC (IPv4 or IPv6)	SII Lawful Intercept (RFC 3924)
IPv6 Phase 3	In-chassis Mixed Annex A & Annex B support
Cable Source Verify with DHCP Lease Query	802.1Q VLAN tagging
Route Injection (RI) for DHCPv6 Prefix Delegation	Extended ACLs & Named ACLs
OSPFv3	Secure Shell v2 (SSHv2)
DOCSIS 3.0 Eight Channel Bonding (Downstream)	DOCSIS Ping
DOCSIS 3.0 Four Channel Bonding (Upstream)	ARP Abuse Counts
Cross-MAC Domain Dynamic Load Balancing	DHCP Relay Agent (Option 82)
Dynamic Cable Modem Load Balancing	DNS Client

Continued on the next page...

# ARRIS Technical Specifications

---

## Ordering Information

Part Number	Description
<b>24U CAM Kits</b>	
790562	24U DOCSIS/EuroDOCSIS™ CAM Kit (Even): 1 x 24U CAM, Even CAM PIC, and SW for C4 CMTS
790563	24U DOCSIS/EuroDOCSIS CAM Kit (Odd): 1 x 24U CAM, Odd CAM PIC, and SW for C4 CMTS
790564	24U DOCSIS/EuroDOCSIS CAM Kit (Spare): 1 x 24U CAM, Spare CAM PIC, and SW for C4 CMTS
794069	24U DOCSIS/EuroDOCSIS CAM Kit (Even): 1 x 24U CAM, Even CAM PIC, and SW for C4c CMTS
794070	24U DOCSIS/EuroDOCSIS CAM Kit (Odd): 1 x 24U CAM, Odd CAM PIC, and SW for C4c CMTS
<b>Maintenance Plan (required)</b>	
708387	Software Maintenance – Phone Plus Gold

---

### Specifications are subject to change without notice.

The capabilities, system requirements and/or compatibility with third-party products described herein are subject to change without notice. ARRIS, the ARRIS logo, Auspice®, BigBand Networks®, BigBand Networks and Design®, BME®, BME 50®, BMR®, BMR100®, BMR1200®, C3™, C4®, C4c™, C-COR®, CHP Max5000®, ConvergeMedia™, Cornerstone®, CORWave™, CXM™, D5®, Digicon®, E6000™, ENCORE®, EventAssure™, Flex Max®, FTTMax™, HEMI®, MONARCH®, MOXI®, n5®, nABLE®, nVision®, OpsLogic®, OpsLogic® Service Visibility Portal™, Opti Max™, PLEXIS®, PowerSense™, QUARTET®, Rateshaping®, Regal®, ServAssure™, Service Visibility Portal™, TeleWire Supply®, TLX®, Touchstone®, Trans Max™, VIPr™, VSM™, and WorkAssure™ are all trademarks of ARRIS Group, Inc. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks and the names of their products. ARRIS disclaims proprietary interest in the marks and names of others. © Copyright 2012 ARRIS Group, Inc. All rights reserved. Reproduction in any manner whatsoever without the express written permission of ARRIS Group, Inc. is strictly forbidden. For more information, contact ARRIS.



[www.arrisi.com](http://www.arrisi.com)