## 8-2160969-0 | FID-SG-080M-01E-XX



Fiber Optic Indoor Drop Cable Assembly, SC/APC to Stub, 3mm, 80M

## **Product Classification**

Regional Availability EMEA

**Product Type** Fiber drop cable assembly

Product Series FID

General Specifications

Cable TypeStapleable - Round

Connector A, quantity 1

Color, boot AGreenColor, connector AGreenInterface, Connector ASC/APCInterface Feature, connector AMale

Interface, Connector B Unterminated

Jacket Color Ivory

Total Fibers, quantity 1

Dimensions

Cable Assembly Length80 m | 262.467 ftCable Outer Diameter3.0 mm (0.12 in)

Material Specifications

Jacket Material Low Smoke Zero Halogen (LSZH)

Mechanical Specifications

Minimum Bend Radius, loaded50 mm1.969 inMinimum Bend Radius, unloaded30 mm1.181 inTensile Load, long term, maximum30 N6.744 lbfTensile Load, short term, maximum100 N22.481 lbf

**COMMSCOPE®** 

## 8-2160969-0 | FID-SG-080M-01E-XX

Cable Crush Resistance, maximum 15 N/mm | 85.652 lb/in

Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

Insertion Loss, maximum, connector A0.4 dBReturn Loss, minimum, connector A65 dB

**Environmental Specifications** 

Installation temperature -20 °C to +60 °C (-4 °F to +140 °F)

Operating Temperature  $-5 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+23  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+75 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +167  $^{\circ}\text{F}$ )

Environmental Space Indoor

Jacket UV Resistance UV stabilized

Packaging and Weights

**Cable weight** 7.9 kg/km | 5.309 lb/kft

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

