## 400BPDM-CR



#### 7-16 DIN Male for CNT-400 and CNT-400-Flex braided cable

#### **Product Classification**

Product Type Braided cable connector

Product Brand CNT®

General Specifications

Body StyleStraightInner Contact Attachment MethodSolderInner Contact PlatingSilver

**Interface** 7-16 DIN Male

 Outer Contact Attachment Method
 Crimp

 Outer Contact Plating
 Trimetal

**Dimensions** 

 Width
 35 mm | 1.378 in


 Length
 38.12 mm | 1.501 in

 Diameter
 35 mm | 1.378 in

Nominal Size 0.405 in

Outline Drawing





### **Electrical Specifications**

**Insertion Loss, typical** 0.05 dB

Average Power at Frequency 580.0 W @ 900 MHz

Cable Impedance50 ohmConnector Impedance50 ohmdc Test Voltage2500 VInner Contact Resistance, maximum1.5 mOhm

Insulation Resistance, minimum 10000 MOhm
Operating Frequency Band 0 - 6000 MHz

**Outer Contact Resistance, maximum** 0.4 mOhm

RF Operating Voltage, maximum (vrms) 894 V

#### VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0-3000 MHz	1.08	28.3
3000-6000 MHz	1.2	20.83



## 400BPDM-CR

#### Mechanical Specifications

**Connector Retention Tensile Force** 330 N | 74.187 lbf

Connector Retention Torque0.56 N-m4.956 in lbCoupling Nut Proof Torque35 N-m309.776 in lb

**Coupling Nut Proof Torque Method** IEC 61169-4:9.3.6

**Coupling Nut Retention Force** 1000 N | 224.809 lbf

**Coupling Nut Retention Force Method** IEC 61169-4:15.2.6

Interface Durability 500 cycles

Interface Durability Method IEC 61169-4:17

Mechanical Shock Test Method IEC 60068-2-27

#### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

**Storage Temperature**  $-65 \,^{\circ}\text{C} \text{ to } +125 \,^{\circ}\text{C} \, (-85 \,^{\circ}\text{F to } +257 \,^{\circ}\text{F})$ 

Attenuation, Ambient Temperature  $20 \, ^{\circ}\text{C} \mid 68 \, ^{\circ}\text{F}$ Average Power, Ambient Temperature  $40 \, ^{\circ}\text{C} \mid 104 \, ^{\circ}\text{F}$ 

**Average Power, Inner Conductor Temperature** 100 °C | 212 °F

Climatic Sequence Test Method IEC 60068-1

Corrosion Test Method IEC 60068-2-11

Damp Heat Steady State Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Water Jetting Test Mating Mated

Water Jetting Test Method IEC 60529:2001, IP65

Packaging and Weights

**Weight, net** 57.2 g | 0.126 lb

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system





# 400BPDM-CR

## \* Footnotes

**Insertion Loss, typical** 0.05v<sup>-</sup>freq (GHz) (not applicable for elliptical waveguide)

