


# 760250638 | FT 2MM PVC SP 1050X1400UM PVDF RD



Furcation Tubing for Optical Fiber, indoor, PVC jacket, PVDF tubing, 1.4/2.0 mm, with strength member, red

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Product Type

Furcation tubing

## General Specifications

### Application

For use with all fiber connector types | For use with singlemode and multimode optical fibers

### Color

Red

## Dimensions

### Length

1000 m | 3,280.84 ft

### Inner Diameter, nominal

1.05 mm | 0.041 in

### Outer Diameter, nominal

2.06 mm | 0.081 in

## Material Specifications

### Material Type

PVC | PVDF

## Mechanical Specifications

### Minimum Bend Radius, Installation

3 mm | 0.118 in

### Minimum Bend Radius, Long Term

5 mm | 0.197 in

### Shrinkage, maximum

5 %

## Environmental Specifications

### Installation temperature

0 °C to +70 °C (-32 °F to +158 °F)

### Operating Temperature

-20 °C to +70 °C (-4 °F to +158 °F)

### Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

### Environmental Space

Indoor

# 760250638 | FT 2MM PVC SP 1050X1400UM PVDF RD

---

## Packaging and Weights

<b>Included</b>	Aramid strength members
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Reel
<b>Weight, net</b>	3 kg/km   2.016 lb/kft

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable