


RFA812-16S06

HELIAX® Hybrid Cable Assembly, 8 power conductors, 16-fiber, black jacket, aluminum armor



OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable assembly
Product Brand	HELIAX®
Product Series	RFA
Ordering Note	CommScope® non-standard product

General Specifications

Conductors, quantity	8
Construction Type	Hybrid standard trunk
Interface, Connector A	DLC
Interface Feature, connector A	Standard
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Feature, connector B	Standard
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	16

Dimensions


Cable Assembly Length Range (m)	5 – 100
--	---------

RFA812-16S06-5M

Diameter Over Jacket 19.81 mm | 0.78 in

Center Conductor Gauge 12 AWG

Ordering Tree



Mechanical Specifications

Minimum Bend Radius 198.1 mm | 7.799 in

Minimum Bend Radius, furcation 30 mm | 1.181 in

Optical Specifications

Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

RFA812-16S06

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Packaging and Weights

Cable weight 0.5 kg/m | 0.336 lb/ft

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)