

# CPC8392

---

## Base Product

GigaSPEED® 110GS to GS8E 4 Pair Low Smoke Zero Halogen Hybrid Patch Cord

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Twisted pair patch cord
<b>Product Brand</b>	GigaSPEED®
<b>Product Series</b>	CPC
<b>Ordering Note</b>	Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords   Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices

## General Specifications

<b>ANSI/TIA Category</b>	6
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type</b>	Stranded
<b>Interface, Connector A</b>	110 plug
<b>Interface Feature, connector A</b>	Standard
<b>Interface, Connector B</b>	RJ45 plug
<b>Interface Feature, connector B</b>	Standard
<b>Jacket Color</b>	Dark gray
<b>Pairs, quantity</b>	4
<b>Transmission Standards</b>	IEEE 802.3bt Type 4
<b>Wiring</b>	T568B

## Dimensions

<b>Cable Assembly Length Range (m)</b>	1 – 30
<b>Cable Assembly Length Range (ft)</b>	1 – 100
<b>Diameter Over Jacket</b>	6.02 mm   0.237 in
<b>Compatible Conductor Gauge, stranded</b>	24 AWG

# CPC8392

## Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	White/Orange
Position 2	Blue	Orange
Position 3	White/Orange	Lt. Green
Position 4	Orange	Blue
Position 5	Lt. Green	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Electrical Specifications

**dc Resistance, maximum**

0.3 ohm

## Ordering Tree

CPC     -

### Outlet Color

0	Not applicable
1	Black
2	Blue
3	Gray
4	Green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac

### Jacket Color

1	Black
2	Light blue
3	Dark gray
4	Spring green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac
C	Gray
K	Pink
L	Violet
M	Green
Z	Blue

### UOM

11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

### Length

12

### Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

## Material Specifications

**Contact Plating Material**

Precious metals

**Material Type**

Copper alloy | Polycarbonate

# CPC8392

---

## Mechanical Specifications

<b>Plug Insertion Life, minimum</b>	200 times
<b>Plug Retention Force, minimum</b>	44 N   9.892 lbf

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	ETL   cETL

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

860087279 3074E WHT C6 4/24 SR U/UTP RVAR	-	GigaSPEED XL® 3074E Category 6 U/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, variable length, reel
---	---	---