# ICX7850-48C | RUCKUS ICX 7850-48C



### High-End 48 Ports 10G BASE-T Chassis Replacement Switch

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Product Type Ethernet switch

Product Brand RUCKUS®

### General Specifications

Switching Capacity, maximum 4000 Gb/s

1/10 GbE 10G BASE-T RJ-45 Ports, quantity, maximum 48

40 GbE QSFP Ports, quantity, maximum 8

100 GbE QSFP28 Ports, quantity, maximum 8

Switches per Stack, maximum 12

Aggregate Stack Bandwidth, maximum 9600 Gb/s

PoE/PoE+ No

**Stacking** Yes

**sFlow** Yes

Layer 3 (STATIC, RIP, OSPF) Yes

OpenFlow with Hybrid Port Mode Yes

Campus Fabric Technology Yes

**Redundant Power Option** Yes

Hot Swap Internal Power Supplies & Fans Yes

**VRF** Yes

**BGP** Yes

Reversible Airflow Option Yes

**VxLAN** Yes

Multi Chassis Trunking (MCT) Yes



# ICX7850-48C | RUCKUS ICX 7850-48C

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

