

NCC44SBJB

Base Product



NCC Cat 6A F/FTP, Plug-to-SLX Jack, (Black), Class B2ca

Product Classification

Regional Availability	EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Product Series	NCC
Ordering Note	Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices

General Specifications

ANSI/TIA Category	6A
Cable Type	F/FTP (shielded)
Conductor Type	Solid
Information Outlet Color	Black Gray White
Interface, Connector A	RJ45 plug
Interface Feature, connector A	Standard
Interface, Connector B	RJ45 jack
Interface Feature, connector B	Standard
Jacket Color	White
Pairs, quantity	4
Transmission Standards	IEEE 802.3bt Type 4
Wiring	T568B

Dimensions

Cable Assembly Length Range (m)	1 – 100
Cable Assembly Length Range (ft)	1 – 328

NCC44SBJB

Diameter Over Jacket 7.01 mm | 0.276 in
Compatible Conductor Gauge, solid 23 AWG

Ordering Tree

NCC - ⁹ ¹⁰ ¹¹ ¹²

Outlet Color

0	Not applicable
1	Black
2	Blue
3	Gray
4	Green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac

Jacket Color

1	Black
2	Light blue
3	Dark gray
4	Spring green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac
C	Gray
K	Pink
L	Violet
M	Green
Z	Blue

UOM

M Meter

Length

XXX

Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance B2ca
EN50575 CPR Cable EuroClass Smoke Rating s1
EN50575 CPR Cable EuroClass Droplets Rating d0
EN50575 CPR Cable EuroClass Acidity Rating a1
Environmental Space Low Smoke Zero Halogen (LSZH)
Safety Standard UL 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

NCC44SBJB

Agency

CENELEC

**Classification**

EN 50575 compliant, Declaration of Performance (DoP) available

Included Products

884048458/16 – CS44ZB Category 6A F/FTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft
CS44ZB WHT C6A 4/23 F/FTP (500 m) length, reel
RL 500M

CS44ZB Category 6A F/FTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft (500 m) length, reel



Product Classification

Regional Availability	EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair cable


General Specifications

Product Number	CS44ZB
ANSI/TIA Category	6A
Cable Component Type	Horizontal
Cable Type	F/FTP (shielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	White
Pairs, quantity	4
Transmission Standards	ANSI/TIA-568.2-D ISO/IEC 11801 Class EA

Dimensions

Cable Length	500 m 1,640.42 ft
Cable Length Tolerance	±5%
Diameter Over Insulated Conductor	1.168 mm 0.046 in
Diameter Over Jacket, nominal	7.01 mm 0.276 in
Jacket Thickness	0.635 mm 0.025 in
Conductor Gauge, singles	23 AWG

Cross Section Drawing



Electrical Specifications

Coupling Attenuation	Type II
dc Resistance Unbalance, maximum	2 %
dc Resistance, maximum	7.61 ohms/100 m 2.32 ohms/100 ft
Mutual Capacitance at Frequency	4.2 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	80 %
Operating Frequency, maximum	500 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
Segregation Class	d
Transfer Impedance	Grade 2

Electrical Cable Performance

CS	CommScope	NEXT	Near End Crosstalk (dB/100m)
STD	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	PSNEXT	Power Sum Near End Crosstalk (db/100m)
TYP	Typical Electrical Performance	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
IL	Insertion Loss (dB/100m)	RL	Return Loss (dB)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
TCL	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL	NEXT	ACR	PSNEXT	PSACR	ACRF	PSACRF	RL	TCL	ELTCTL
	TYP	TYP	TYP	TYP	TYP	TYP	TYP	TYP	TYP	TYP
1	1.9	98.4	96.5	96.6	94.6	98.9	96.6	29	61.9	61.7
4	3.5	99.9	96.3	97.8	94.2	98.2	95.6	30.1	55.9	56.1
8	4.9	96.1	91.2	93.8	88.9	94.6	92.1	34.9	57.2	56.6
10	5.5	95.5	90.1	93.3	87.9	92.2	89.8	34.8	54.1	53.7
16	6.9	93	86	90.7	83.8	89.1	86.5	35.9	51.6	51.9
20	7.8	90	82.2	87.6	79.8	88.3	85.8	35.8	52.8	52
25	8.8	88.5	79.7	86.1	77.3	87.1	84.7	34.6	51.6	51.3
31.25	9.9	88.7	78.8	86.2	76.3	85.5	83.1	32.7	50.7	
62.5	14.1	86.1	72	83.9	69.7	79.7	77.4	30	46.5	
100	17.9	79.8	61.9	78.4	60.5	70.9	68.9	27	43.8	
155	22.4	82.1	59.8	79.9	57.6	69.1	66.9	23.4	40.9	
200	25.5	79.6	54.1	77.5	52	62	59.9	21	39.1	
250	28.6	76.1	47.5	74.3	45.7	63.9	61.4	19	36.5	
300	31.4	70.9	39.5	69.6	38.2	62.2	59.9	18	35.9	
350	34.1	73.4	39.4	72	37.9	55.6	53.5	16.9	35	
400	36.4	73.2	36.8	71.4	35	54.4	52.3	16	34	
500	41.1	68.8	27.7	67.1	26.1	42.9	40.7	15.2	33.1	
600	45.3	67.6	22.3	65.7	20.4	43.5	41.1	12.9	31.7	
650	47.1	65.4	18.3	63.5	16.4	38.9	36.6	12.4	31.4	

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	Low Smoke Zero Halogen (LSZH)
Shield (Tape) Material	Polyester/Aluminum shield

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

884048458/16 | CS44ZB WHT C6A 4/23 F/FTP RL 500M

Installation temperature	0 °C to +50 °C (+32 °F to +122 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Acid Gas Test Method	EN 50267-2-3
EN50575 CPR Cable EuroClass Fire Performance	B2ca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d1
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Low Smoke Zero Halogen (LSZH)
Smoke Test Method	IEC 61034-2

Packaging and Weights

Cable weight	48,514.145 kg/km 32600 lb/kft
Packaging Type	Reel

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

