

SVA15PRSMS



HomeConnect® Mini Subscriber Amplifier, 15 dB, one port, all ports down

OBSOLETE

Product Classification

Product Type	RF amplifier
Product Brand	HomeConnect®

General Specifications

Device Type	Subscriber amplifier
Application	Indoor Outdoor
Video Ports, quantity	1
Video Standard	NTSC

Electrical Specifications

Distortion Performance (CCN), minimum	70 -dBc
Distortion Performance (CSO), minimum	65 -dBc
Distortion Performance (CTB), minimum	75 -dBc
Distortion Performance (X-Mod), minimum	75 -dB
Group Delay, channel 2–4, maximum	20 ns
Group Delay, channel 5–6, maximum	5 ns
Group Delay, reverse, maximum	20 ns
Hum Modulation, minimum	-75 dB
Impedance	75 ohm
Operating Current at Voltage	200 mA @ 12 Vdc
Shielding Effectiveness, minimum	100 dB

SVA15PRSMS

Surge Capability Test Method

ANSI/SCTE 81 | IEEE C62.41-A3 (6 kV, 200 A, Ring wave) on all ports | IEEE C62.41-B3 (6 kV, 3000 A, Combination wave) on input port

Surge Capability Waveform

1.2/50 voltage and 8/20 current combination waveform | 100 kHz ring wave waveform

Electrical Specifications, Isolation

Isolation at Frequency Band, power port to RF output, minimum

55 dB @ 5–1002 MHz

Electrical Specifications, Rx (Uplink)

Flatness

±0.5 dB

Insertion Loss, maximum

1.2 dB

Return Loss, minimum

20 dB

Operating Frequency Band

5 – 42 MHz

Electrical Specifications, Tx (Downlink)

Flatness

±1.0 dB

Gain

15 dB

Noise Figure, maximum

4 dB

Operating Frequency Band

53 – 1002 MHz

Return Loss, minimum

20 dB

Environmental Specifications

Operating Temperature

-40 °C to +60 °C (-40 °F to +140 °F)

Safety Standard

CE | SCTE

Packaging and Weights

Height, packed

190.5 mm | 7.5 in

Width, packed

228.6 mm | 9 in

Length, packed

469.9 mm | 18.5 in

Carton Quantity

20

Included

Power adapter

Weight, gross

7.711 kg | 17 lb

Regulatory Compliance/Certifications

Agency

Classification

SVA15PRSMS

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

SVAPA12V200	–	HomeConnect® Power Adapter for Subscriber Amplifiers, ac/dc, 12 V, 200 mA
-------------	---	---

* Footnotes

Distortion Performance (CCN), minimum	CCN—Composite Carrier to Noise; 77 analog, 110 digital—256 QAM channel loading
Distortion Performance (CSO), minimum	CSO—Composite Second Order; 77 analog, 110 digital—256 QAM channel loading
Distortion Performance (CTB), minimum	CTB—Composite Triple Beat; 77 analog, 110 digital—256 QAM channel loading
Distortion Performance (X-Mod), minimum	X-Mod—Cross Modulation; 77 analog, 110 digital—256 QAM channel loading
Group Delay, channel 2–4, maximum	Channel 2 (3.58 MHz Span)
Group Delay, channel 5–6, maximum	Channel 4–6 (3.58 MHz Span)
Noise Figure, maximum	Total amplifier contribution

SVAPA12V200



HomeConnect® Power Adapter for Subscriber Amplifiers, ac/dc, 12 V, 200 mA

Product Classification

Product Type	RF amplifier power adapter
Product Brand	HomeConnect®

General Specifications

Plug Type	Type A
------------------	--------

Electrical Specifications

Input Current, maximum	50 mA
Input Voltage @ Voltage at Frequency	120 Vac @ 60 Hz
Output Voltage Tolerance, no load	±5%
Output Voltage, no load	20.2 Vdc
Operating Current at Voltage	200 mA @ 12 Vdc

Environmental Specifications

Safety Standard	c-UL-us
------------------------	---------

Packaging and Weights

Height, packed	292.1 mm 11.5 in
Width, packed	279.4 mm 11 in
Length, packed	444.5 mm 17.5 in
Carton Quantity	100
Weight, gross	18.144 kg 40 lb

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

SVAPA12V200

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

