
## 760253116 | N-008-MP-5K-F08AQ/20T/B2



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk with 2.0mm Subunits, 8 fiber, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color, B2ca flame rating

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA

8

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series N-MP

## General Specifications

Cable TypeMPO trunk cableConstruction TypeNon-armoredSubunit TypeGel-freeJacket ColorAquaJacket MarkingFeetSubunit, quantity1

#### **Dimensions**


**Total Fiber Count** 

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket5.3 mm | 0.209 in

## Representative Image



## 760253116 | N-008-MP-5K-F08AQ/20T/B2



## Mechanical Specifications

Minimum Bend Radius, loaded 80 mm | 3.15 in

Minimum Bend Radius, unloaded 53 mm | 2.087 in

**Tensile Load, long term, maximum** 133 N | 29.9 lbf

**Tensile Load, short term, maximum** 445 N | 100.04 lbf

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 412 m | 1,351.706 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550

**Environmental Specifications** 

**Installation temperature** 0 °C to +60 °C (+32 °F to +140 °F)

Page 2 of 5



# 760253116 | N-008-MP-5K-F08AQ/20T/B2

 $\begin{tabular}{ll} \textbf{O °C to +70 °C (+32 °F to +158 °F)} \end{tabular}$ 

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

**Environmental Space** Low Smoke Zero Halogen (LSZH)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2

**Environmental Test Specifications** 

**Low High Bend**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** 0 °C to +70 °C (+32 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 33 kg/km | 22.175 lb/kft

#### Included Products

CS-5K-MP – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



## LazrSPEED® 550 LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

#### **Product Classification**

PortfolioCommScope®Product TypeOptical fiber

## General Specifications

**Cladding Diameter** 125 µm **Cladding Diameter Tolerance** ±0.8 µm **Cladding Non-Circularity, maximum** 1 % **Coating Diameter (Colored)** 254 µm **Coating Diameter (Uncolored)** 245 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±10 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm Core/Clad Offset, maximum  $1.5 \, \mu m$ 

**Proof Test** 689.476 N/mm<sup>2</sup> | 100000 psi

## Mechanical Specifications

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

 Macrobending, 75 mm Ø mandrel, 100 turns
 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

Coating Strip Force, maximum $8.9 \,\mathrm{N}$  |  $2.001 \,\mathrm{lbf}$ Coating Strip Force, minimum $1.3 \,\mathrm{N}$  |  $0.292 \,\mathrm{lbf}$ 

**Dynamic Fatigue Parameter, minimum** 18

## Optical Specifications

 Numerical Aperture
 0.2

 Numerical Aperture Tolerance
 ±0.015

 Point Defects, maximum
 0.15 dB

Page 4 of 5

## CS-5K-MP

**Zero Dispersion Slope, maximum** 0.105 ps/[km-nm-nm]

**Zero Dispersion Wavelength, maximum** 1316 nm **Zero Dispersion Wavelength, minimum** 1297 nm

## Optical Specifications, Wavelength Specific

**1 Gbps Ethernet Distance** 1,110 m @ 850 nm | 600 m @ 1,300 nm

**10 Gbps Ethernet Distance** 550 m @ 850 nm

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

**Backscatter Coefficient** -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm

 Bandwidth, Laser, minimum
 4,700 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

 Bandwidth, OFL, minimum
 3,500 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

**Differential Mode Delay** 0.70 ps/m @ 850 nm | 0.88 ps/m @ 1,300 nm

Differential Mode Delay Note Superior to TIA-492AAAC and IEC 60793-2-10 at 850 nm

**Index of Refraction** 1.479 @ 1,300 nm | 1.483 @ 850 nm

**Standards Compliance** IEC 60793-2-10, type A1a.3a | IEC 60793-2-10, type A1a.3b | TIA-

492AAAD (OM4)

## **Environmental Specifications**

Heat Aging, maximum 0.20 dB/km @ 85 °C

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.2 dB/km

**Water Immersion, maximum** 0.20 dB/km @ 23 °C

## Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



### \* Footnotes

**Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

**Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

**COMMSCOPE®**