

H5PNM-S



Type N Male with gas barrier for 7/8 in HJ5-50 air dielectric cable

OBSOLETE

Product Classification

Product Type	Air coaxial connector
Product Brand	HELIAX®

General Specifications

Body Style	Straight
Cable Family	HJ5-50
Gas Barrier	Yes
Inner Contact Attachment Method	Spring fingers
Inner Contact Plating	Silver
Interface	N Male
Mounting Angle	Straight
Outer Contact Attachment Method	Tab-flare
Outer Contact Plating	Silver

Dimensions

Length	83.058 mm 3.27 in
Diameter	41.402 mm 1.63 in
Nominal Size	7/8 in

Electrical Specifications

Insertion Loss, typical	0.05 dB
Average Power at Frequency	0.6 kW @ 900 MHz

H5PNM-S

Cable Impedance	50 ohm
Connector Impedance	50 ohm
dc Test Voltage	2 kV
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 5200 MHz
Peak Power, maximum	10 kW
RF Operating Voltage, maximum (vrms)	707 V

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0–1000 MHz	1.02	40.09
1000–2200 MHz	1.025	38.17
2200–4000 MHz	1.08	28.3
4000–5200 MHz	1.15	23.13

Mechanical Specifications

Interface Durability	500 cycles
Interface Durability Method	MIL-C-39012, Section 4.6.12
Mechanical Shock Test Method	MIL-STD-202, Method 213, Test Condition I

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)
Corrosion Test Method	MIL-STD-202, Method 101, Test Condition B
Moisture Resistance Test Method	MIL-STD-202, Method 106
Thermal Shock Test Method	MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C
Vibration Test Method	MIL-STD-202, Method 204, Test Condition B

Packaging and Weights

Weight, net	0.33 kg 0.728 lb
--------------------	--------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

H5PNM-S

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Insertion Loss, typical 0.05√freq (GHz) (not applicable for elliptical waveguide)