



FIST™ Splice/patch Sub-assembly kit with 2 trays, each for holding up to 2 fiber adapters and 8 splice protectors

- Splice sub-assemblies consists of a wraparound groove plate holding the included splice organizer trays
- Groove plates are designed with slots for routing fiber to and from the organizer trays

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Fiber splice/patch tray

General Specifications

Application For use with FIST MK2 organizers

Color Gray

Splice Tray Chip Type Heat shrink

Splice Tray Construction MS (Mass splicing for up to 8 primary/secondary coated fibers) | SP (Single patch for up to 2 SC or 4 LC adapters)

Splice Tray Included, quantity 2

Splices per Tray, note 8 splices (250/900µm) per tray

Splices per Tray, quantity 8

Dimensions

Height 152 mm | 5.984 in

Width 105 mm | 4.134 in

Depth 12 mm | 0.472 in

Fiber Storage Length, maximum 800 mm for mixed 250/900 µm fibers

Fiber Storage Length, minimum 650 mm | 25.591 in

Splice Protector Length, maximum 45 mm | 1.772 in

Splice Protector Length, minimum 45 mm | 1.772 in

Splice Protector Diameter, maximum 2.8 mm | 0.11 in

Splice Protector Diameter, minimum 2.8 mm | 0.11 in

Material Specifications

760240238 | FIST-SOSA2-2SP-S

Material Type PBT | PET

Mechanical Specifications

Minimum Bend Radius, standard 15 mm | 0.591 in

Environmental Specifications

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity 93%, non-condensing

Environmental Space Indoor | Outdoor

Packaging and Weights

Packaging quantity 1

Packaging Type Bag

Weight, net 0.1 kg | 0.22 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

