

FA-17MM-114-RM



1 1/4 in Double Hanger Kit for HELIAX® Direct Power tails, 17 mm grommet, round member adapter (75-100 mm), clamp head, triple stack, kit of 10

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	6
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	3
Height	184.4 mm 7.26 in
Width	28.7 mm 1.13 in
Length	120.4 mm 4.74 in
Compatible Cable Diameter Range	16–17 mm
Compatible Diameter, maximum	17 mm 0.669 in
Compatible Diameter, minimum	16 mm 0.63 in

Material Specifications

Material Type	Corrosion proof coated metal Engineered plastic
----------------------	---

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
---------------------------	--------------------------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

FA-17MM-114-RM

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Packaging quantity	10
---------------------------	----

Included Products

31670-3	-	Round Member Adapter for 3–4 in round members
DHK-114-6-P	-	Double Hanger Kit for 1-1/4 in coaxial cable, triple stack; includes hardware and angle adapter
HG-58-114	-	Grommet with 19mm hole for 1-1/4 in SnapStak or polymer block hanger
MF39901-10	-	Clamp Head

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

31670-3



Round Member Adapter for 3–4 in round members

Product Classification

Product Type	Adapter
Ordering Note	CommScope® standard product (Global)

General Specifications

Adapter Type	Round member adapter
---------------------	----------------------

Dimensions

Compatible Diameter, maximum	101.6 mm 4 in
Compatible Diameter, minimum	76.2 mm 3 in
Material Thickness	0.711 mm 0.028 in

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Maximum Loading	Triple stack, 1-5/8 in cable
------------------------	------------------------------

Packaging and Weights

Height, packed	14.2 cm 5.591 in
Width, packed	14.2 cm 5.591 in
Length, packed	7.9 cm 3.11 in
Packaging quantity	10
Weight, gross	0.31 kg 0.683 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

31670-3

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant



DHK-114-6-P



Double Hanger Kit for 1-1/4 in coaxial cable, triple stack; includes hardware and angle adapter

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa

General Specifications

Cables per Hanger	6
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	3
Height	184.4 mm 7.26 in
Width	25.9 mm 1.02 in
Length	120.4 mm 4.74 in
Compatible Diameter, maximum	40.1 mm 1.579 in
Compatible Diameter, minimum	38.1 mm 1.5 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

DHK-114-6-P

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 31.8 cm | 12.52 in

Width, packed 31.8 cm | 12.52 in

Length, packed 7.6 cm | 2.992 in

Included Angle adapter | Hardware

Packaging quantity 1

Weight, gross 0.48 kg | 1.058 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

HG-58-114



Grommet with 19mm hole for 1-1/4 in SnapStak or polymer block hanger

Product Classification

Product Type	Grommet
Ordering Note	CommScope® standard product (Global)

General Specifications

Adapter Type	Adapter
Cables per Hanger	1
Color	Black

Dimensions

Height	55.626 mm 2.19 in
Diameter Range (cable 1)	19 mm
Nominal Size	1-1/4 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Packaging and Weights

Packaging quantity	10
Weight, gross	0.74 kg 1.631 lb

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

MF39901-10



Clamp Head

Product Classification

Product Type	Clamp set
Ordering Note	CommScope® non-standard product

General Specifications

Adapter Type	Adapter
Mounting	3/8 in through hole

Dimensions

Outside Width	73.152 mm 2.88 in
Outside Length	19.05 mm 0.75 in
Material Thickness	2.591 mm 0.102 in

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Maximum Loading	Triple stack, 1-5/8 in cable
------------------------	------------------------------

Packaging and Weights

Height, packed	5 cm 1.969 in
Width, packed	8 cm 3.15 in
Length, packed	1 cm 0.394 in
Packaging quantity	10
Weight, gross	0.25 kg 0.551 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

MF39901-10

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

