

Touchstone TM3402B

DOCSIS / EuroDOCSIS 3.1 Telephony Modem

FEATURES

- 2x2 OFDM/OFDMA DOCSIS® / EuroDOCSIS® 3.1 channels
- 32x8 SC-QAM DOCSIS® / EuroDOCSIS® 3.0 channels
- Full Capture Bandwidth Tuner
- Switchable US filter options include: 5-85MHz or 5-204MHz
- Switchable DS filter options include: 108-1218MHz or 258-1218MHz
- Multi Processor Technology (ARM and ATOM based Application Processor)
- 4 Port Gigabit Ethernet LAN and 2 RJ-11 VoIP ports
- Support for NCS, Legacy SIP, and PacketCable™ 2.0/1.5/1.0 signaling
- Multiple L2VPN BSoD support with OAM extensions
- PNM based network monitoring and diagnostics
- DS / US spectrum analyzer functionality



PRODUCT OVERVIEW


The TM3402B DOCSIS / EuroDOCSIS 3.1 implementation allows unprecedented data rates to be delivered to MSO customers, along with two lines of VoIP service based on PacketCable™ specifications. The TM3402B is designed to enable deployment of Gigabit+ data services. Switchable US/DS filters provide for superior RF performance, reduce the potential for interference in the home network, and allows the flexibility required for MSO transitions in cable frequency plans. Increased memory allows new applications to be deployed on the modem. Overall, this feature-packed unit is intended to serve as the hub of a subscriber network, connecting all IP-capable devices (Internet, Data, Voice and Video) throughout the customer premises.

With residential high-speed data service, MSO support becomes a top concern. The TM3402B distinguishes itself by providing tools to minimize the complexity of support. US and DS spectrum analysis along with proactive network management based diagnostics take the monitoring and diagnostic capabilities of the TM3402B to a premium level. OAM extensions to L2VPN allow for system-level provisioning and diagnostics. Multiple provisioning methods (SNMP, Configuration File, WebGUI access) allow custom-designed setup to be applied to monitor the end user more efficiently. Multiple remote access levels also ease manual configuration and control. The TM3402B is defining the future for advanced residential and SOHO services.

Touchstone TM3402B DOCSIS / EuroDOCSIS 3.1 Telephony Modem



DOCSIS 3.0 vs DOCSIS 3.1 Speeds



SPECIFICATIONS

Physical

Operating Temp (°C)	0 – 40
Operating Relative Humidity	5-85% (Non-Condensing)
Storage Temp (°C)	-40 to 70
Dimensions, HxWxD (in)	7.6 x 2.1 x 6.2
Weight (lbs) °C	1.1
Diagnostic LEDs (Front)	Power, DS/US, Online, Tel1, Tel2
Diagnostic LEDs (Rear)	Ethernet Link/Speed

Interfaces

RF Interface	1 External 'F' Connector
Data Interfaces (Bridged)	4x 10/100/1000 Base-T Ethernet RJ-45
Telephone Interfaces	2x VoIP RJ-11
Input Voltage (Nominal)	12VDC, 2.5A (adapter) 100-240V, 50/60Hz, 0.8A

Voice

Standards Supported	PC2.0/1.5/1.0, RFC-3261
CODECs Supported	G.711, G.722, G.729
FAX	T.38
REN Capability	5 REN / Line, 10 REN Total
Line Card Support	Flexible LC Templates

SPECIFICATIONS

RF Downstream

Bonded Channels	Up to 32 SC-QAM and/or 2 OFDM
Tuner Configuration	Full Capture Tuning Range
Frequency Range (MHz)	108-1218 or 258-1218
Data Rate (Gbps, Max)	5.0
RF Input Sensitivity Level (dBmV)	-15 to +15 (DOCSIS)

RF Upstream

Bonded Channels	Up to 8 SC-QAM and/or 2 OFDMA
Frequency Range (MHz)	5-85 or 5-204
Configurable Duplex Filter (MHz)	Mid or High split options
<i>Note – US/DS switches automatically together to avoid US/DS overlap</i>	
Data Rate (Gbps Max)	> 1.0
RF Output Level (dBmV)	+65 (64QAM, single US) +57 (64QAM, 4-8 US) +65 (16QAM, single US) +65 (OFDMA)

ORDERING NUMBERS

1000553	TM3402B/CE-204; EuroDOCSIS 3.1 eMTA, 5-85/204MHz US, 108/258-1218MHz DS, 2x RJ-11, 4x GigE, AC/DC Adapter (100-240VAC, 50/60Hz, 12V@2.5A, CEE7/16 Plug), No USB, RoHS
---------	---

CUSTOMER CARE

Contact Customer Care for product information and sales:

- United States: 866-36-ARRIS
- International: +1-678-473-5656