

# SV05



HomeConnect® Test Probe, 20 dB, power blocked, 1 GHz

**OBSOLETE**

## Product Classification

<b>Product Type</b>	Tool
<b>Product Brand</b>	HomeConnect®

## General Specifications

<b>Application</b>	Allows RF probing with 20 dB attenuation of KS port to "F" connector for servicing
--------------------	--

## Electrical Specifications

<b>Insertion Loss</b>	20 dB
<b>Return Loss, input, minimum</b>	15 dB
<b>Frequency Response</b>	±1.0 dB
<b>Impedance</b>	75 ohm
<b>Operating Frequency Band</b>	5 – 1002 MHz
<b>Shielding Effectiveness, minimum</b>	100 dB

## Material Specifications

<b>Material Type</b>	Brass
<b>Plating</b>	Nickel

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Safety Standard</b>	CE   EN 60728-4   SCTE

# SV05

---

## Packaging and Weights

<b>Height, packed</b>	177.8 mm   7 in
<b>Width, packed</b>	241.3 mm   9.5 in
<b>Length, packed</b>	317.5 mm   12.5 in
<b>Carton Quantity</b>	200
<b>Weight, gross</b>	13.61 kg   30.005 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

