


# DDM-M



## Discrete Distribution Module M-Series

### Product Classification

#### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

#### Portfolio

CommScope®

#### Product Type

RJ45 patch panel

### General Specifications

#### Color

Black

#### Rack Type

EIA 19 in

#### Wiring

T568A | T568B

### Dimensions

#### Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

#### Compatible Diameter Over Dielectric, minimum

0.762 mm | 0.03 in

### Electrical Specifications

#### Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

#### Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

#### Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

#### Insulation Resistance, minimum

500 mOhm

### Material Specifications

#### Material Type

High-impact, flame retardant, thermoplastic | Powder-coated steel

### Environmental Specifications

#### Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

#### Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

# DDM-M

---

<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL