### HCCO-1ADDLOA



EHD-1U Pre-stubbed Patch Panel with LC/UPC Adapter and 144f I/O, Riser/LSZH rollable ribbon cable, right cable entry, singlemode with cable length in meters from 25m to 400m in 25m increments

### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel

Product Series EHD

### General Specifications

ColorBlackInterface, frontLC/UPCInterface, rearStub tail

Rack Units 1

**Shelf Movement** Sliding **Total Ports, quantity** 144

#### **Dimensions**

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in

 Depth
 465.84 mm | 18.34 in

 Cable Length
 25 m | 82.021 ft

### **Optical Specifications**

Fiber Mode Singlemode

**Fiber Type** G.657.A2 | OS2

**Insertion Loss, maximum** 0.35 dB

### **Environmental Specifications**

Safety Standard UL 60950


COMMSCOPE®

# HCCO-1ADDLOA

### Included Products

760239307 N-144-CN-RR-F12YL/8G1/99G /C Fiber indoor cable, All-Dielectric, LSZH, Riser-Rated, Gel-Free, Central Tube Rollable Ribbon, 144 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Cca flame rating





Fiber indoor cable, All-Dielectric, LSZH, Riser-Rated, Gel-Free, Central Tube Rollable Ribbon, 144 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Cca flame rating

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** N-CN

General Specifications

Cable Type Ribbon central tube

Construction Type Non-armored

**Subunit Type** Gel-free

Fibers per Ribbon, quantity 12

Jacket Color Yellow

Jacket Marking Feet

Total Fiber Count 144

Dimensions


**Buffer Tube/Subunit Diameter** 6.1 mm | 0.24 in

**Diameter Over Jacket** 10.5 mm | 0.413 in

Representative Image



77 mm | 3.031 in



### Mechanical Specifications

Minimum Bend Radius, unloaded

Minimum Bend Radius, loaded 216 mm | 8.504 in

Minimum Bend Radius, storage coils 432 mm | 17.008 in

Tensile Load, long term, maximum 800 N | 179.847 lbf

**Tensile Load, short term, maximum** 2700 N | 606.984 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Optical Specifications

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

**Environmental Specifications** 

Installation temperature  $-20 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

Page 4 of 6



Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-104-696 | EN 187105 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method CSA FT4 | IEC 60332-1-2 | IEC 60754-2 | IEC 61034-2 | UL

1666 | UL 1685

Water Penentration 24 h

**Water Penentration Test Method** FOTP-82 | IEC 60794-1 F5

**Environmental Test Specifications** 

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Heat Age -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

**Low High Bend**  $-20 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F}\right)$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 122 kg/km | 81.98 lb/kft

### Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 5 of 6





### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

