


CML-H60-B



Heavy Duty Chain Mount Base Kit with Stand-off, 16 ft chain

OBSOLETE

Product Classification

Product Type Chain mount kit

General Specifications

Chains, quantity 4

Pipe, quantity 0

Sectors, quantity 1

Dimensions

Height 152.4 mm | 6 in

Width 203.2 mm | 8 in

Length 203.2 mm | 8 in

Chain Length 4,902.2 mm | 193 in

Mounting Diameter, maximum 1524 mm | 60 in

Mounting Diameter, minimum 203.2 mm | 8 in

Pipe Outer Diameter 114.3 mm | 4.5 in

Mounting Circumference, maximum 4,775.2 mm | 188 in

Mounting Circumference, minimum 635 mm | 25 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

CML-H60-B

Wind Rating	125 mph (BWS) at 100 ft AGL
Wind Rating Criteria	One 8 ft standard microwave antenna, with radome and stiff arm
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Included	Chains
Packaging quantity	1
Weight, net	49.6 kg 109.349 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--