

SZ4999703

Coaxial Drop Cable, 75 Ohm, Series 11, black PVC jacket with APD® floodant



Product Classification

Product Type	Coaxial drop cable
Product Series	11 Series
Warranty	One year

General Specifications

Cable Type	Series 11
Center Conductor Type	Solid
Jacket Color	Black
Jacket Marking	Meters
Performance Note	Attenuation listed represents maximum values at standard condition of 20 °C (68 °F)
Shield Construction Type	Dual shield

Dimensions

Diameter Over Center Conductor, nominal	1.626 mm 0.064 in
Diameter Over Dielectric, nominal	7.112 mm 0.28 in
Diameter Over Inner Shield (Tape), nominal	7.29 mm 0.287 in
Diameter Over Jacket, nominal	10.16 mm 0.4 in
Jacket Thickness, nominal	1.067 mm 0.042 in
Center Conductor Gauge	14 AWG
Inner Shield (Braid) Gauge	34 AWG

Electrical Specifications

Capacitance	53.15 pF/m 16.2 pF/ft
Characteristic Impedance	75 ohm

SZ4999703

Characteristic Impedance Tolerance	±3 ohm
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	41.011 ohms/km 12.5 ohms/kft
dc Resistance, Loop, nominal	63.976 ohms/km 19.5 ohms/kft
dc Resistance, Outer Conductor, nominal	22.966 ohms/km 7 ohms/kft
Nominal Velocity of Propagation (NVP)	85 %
Operating Frequency Band	5–3000 MHz
Structural Return Loss, Grade A	≥15 dB @ 1801–3000 MHz ≥20 dB @ 5–1800 MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	1.25	0.38
55.0	3.15	0.96
83.0	3.87	1.18
85.0	3.9	1.19
187.0	5.74	1.75
204.0	6.14	1.87
211.0	6.23	1.9
250.0	6.72	2.05
300.0	7.38	2.25
350.0	7.94	2.42
400.0	8.53	2.6
450.0	9.02	2.75
500.0	9.51	2.9
550.0	9.97	3.04
600.0	10.43	3.18
750.0	11.97	3.65
865.0	13.05	3.98
1000.0	14.27	4.35
1218.0	16.14	4.92
1300.0	16.44	5.01
1400.0	17.13	5.22
1500.0	17.79	5.42
1600.0	18.44	5.62

SZ4999703

1700.0	19.08	5.81
1794.0	19.66	5.99
1800.0	19.7	6
2000.0	20.89	6.37
2200.0	22.05	6.72
2500.0	23.7	7.22
2800.0	25.28	7.71
3000.0	26.3	8.02

Material Specifications

Center Conductor Material	Copper-clad steel
Dielectric Material	Foam PE
Jacket Material	PVC
Inner Shield (Braid) Coverage	60 %
Inner Shield (Braid) Material	Aluminum
Inner Shield (Tape) Material	Aluminum/Polymer/Aluminum (APA) bonded

Environmental Specifications

Corrosion Protection	APD®
Environmental Space	Outdoor
Flame Test Listing	IEC 60332-1-2

Packaging and Weights

Packaging Type	Reel
Weight, gross	87.802 kg/km 59 lb/kft