

CV5841-000 | FIST-FSASA3-SC-108-2P-S



FIST® Fiber Splice Tray with Field Installable Splitter, symmetrical ratio, two 1x8, Low loss Planar, grade P

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin America | North America

Product Type

Splitter splice tray

Product Brand

FIST®

Product Series

FIST-FSASA3

General Specifications

Functionality

Splitting

Technology Type

Planar lightwave circuit (PLC)

Application

For use with BUDI fiber wall boxes | For use with FIST fiber splice closures

Distribution Type

1 x 8 splitter (2)

Interface, Input

Stub tail

Interface, Output

Stub tail

Split Ratio

Symmetrical

Splitter, quantity

2

Dimensions


Pigtail Diameter

0.25 mm | 0.01 in

Pigtail Diameter, Input

0.25 mm | 0.01 in

Representative Image



Optical Specifications

Directivity, minimum	55 dB
Performance Grade	Grade P (PLC, standard)
Polarization Dependent Loss, maximum	0.2 dB
Uniformity, maximum	1 dB
Wavelength Range	1260–1650 nm
Insertion Loss, Splitter, maximum	10.4 dB
Return Loss, Splitter, minimum	55 dB

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

