ARGRPRG7R

Base Product



Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 UPC (Non-Pinned) to MPO16 (Non-Pinned), Fiber Array Cable Assembly, 16-Fiber, Dual Rated (OFNR/LSZH)

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber array cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Connector A, quantity

Color, boot A Black
Color, connector A Green

Connector B, quantity

Color, boot BBlackColor, connector BGreenConstruction TypeStrandedFurcation ColorYellow

Interface, Connector A MPO-16/APC Female

Interface, Connector B MPO-16/APC Female

Jacket Color Yellow

Polarity Method A

Fibers per Subunit, quantity 16

Total Fibers, quantity 16


COMMSC PE®

ARGRPRG7R

Dimensions

Cable Assembly Length Range (m) 1 - 305Cable Assembly Length Range (ft) 1 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

G.657.A2, TeraSPEED® Fiber Type

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F) **Environmental Space** Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Classification Agency

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser for Light Duty MPO 760251072 N-016-MP-8G1-F30YL/D

Patchcords, 16 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca

flame rating

Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, unpinned, green, for 3 mm 860661399

COMMSC PE

760251072 | N-016-MP-8G1-F30YL/D



Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser for Light Duty MPO Patchcords, 16 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored


Subunit TypeGel-freeJacket ColorYellowJacket MarkingFeet

Total Fiber Count 16

Dimensions

Diameter Over Jacket 3 mm | 0.118 in

Representative Image





760251072 | N-016-MP-8G1-F30YL/D

Mechanical Specifications

Minimum Bend Radius, loaded45 mm1.772 inMinimum Bend Radius, unloaded24 mm0.945 inTensile Load, long term, maximum80 N | 17.985 lbfTensile Load, short term, maximum267 N | 60.024 lbf

Compression 4 N/mm | 22.841 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type G.657.A2/B2

Environmental Specifications

Installation temperature $0 \, ^{\circ}\text{C} \, \text{to} + 60 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 140 \, ^{\circ}\text{F})$ Operating Temperature $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Storage Temperature $-40 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

Page 4 of 7



760251072 | N-016-MP-8G1-F30YL/D

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 8.8 kg/km | 5.913 lb/kft

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



860661399



Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, unpinned, green, for 3 mm cable

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®
Product Type Fiber connector

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Female

Interface Feature Unpinned

Dimensions

Agency

Compatible Cable Diameter 3 mm | 0.118 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2
Insertion Loss, maximum 0.3 dB

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

CHINA-ROHS	Below maximum concentration value
100 0001 001 5	

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

COMMSCOPE®

860661399

ROHS UK-ROHS Compliant Compliant





COMMSCOPE®