



- 1.0 GENERAL NOTES
 - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X.X]
 - 1.2 FEATURES CRITICAL TO QUALITY ARE INDICATED IN ROUNDED BOX (X.X)
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
 - 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD.
- 4.0 TEST
- 5.0 PACKAGING
 - 5.1 PACKAGING MUST BE AGREED TO IN WRITING BY COMMSCOPE PRIOR TO MASS-PRODUCTION APPROVAL.
 - 5.2 PARTS ARE TO BE PACKAGING IN A MANNER OT PREVENT DAMAGE DURING SHIPMENT & STORAGE.
 - 5.3 PACKAGING TO ADHERE TO ALL COMMSCOPE, LOCAL & FOREIGN (WHERE APPLICABLE) SHIPPING REQUIREMENTS.
 - 5.4 PACKAGING & PARTS TO BE FREE OF ALL CONTAMINANTS INCLUDING PAPER FROM BOX, DIRT, DUST, OILS, MOLD RELEASE, DETERGENT AND ALL OTHER FOREIGN MATERIALS.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	JL1183 19DEC22	JW1064 40157351CMO
B	ADDED NOTE	JL1183 07MAR23	JW1064 40167376CMO
C	REDESIGNED MODEL	YMENG 23MAY23	JX1030 40171556CMO

FIT ϕ 2.375" O.D. TO ϕ 3.0" O.D. PIPE
(NOT INCLUDED IN THIS KIT)



ASSEMBLY TOP VIEW



INSTALLATION ASSEMBLY

COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;
INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	PGCS-1000	CLAMP,FRONT-REAR, POLYMER 4CP	2
2	PGCS-4000	PANEL, POLYMER, 2CP	2
3	9615-15	BOLT,CARRIAGE,3/8-16,3,STL GALV	2
4	GW-03	3/8" FLAT WASHER	2
5	GWL-03	3/8" GALV LOCK WASHER	2
6	GN-03	3/8" GALV HEX NUT	2

DENSITY	0.92	lbs/in ³
MASS	0.92	lbs
VOLUME	21.35	in ³
SURFACE AREA	338.56	in ²
HEIGHT	5.0"	
LENGTH	6.6"	
WIDTH	2.0"	

COMMSCOPE, INC. OF NORTH CAROLINA											
TOLERANCES						SAP MATERIAL MASTER					
1 PLACE .X[X] ± 0.2[6.3]			3 PLACE .XXX[X] ± 0.060[1.5]			PGP-CS04					
2 PLACE .XX[X] ± 0.12[3.0]			ANGLES ± 2°			FINISH					
MATERIAL						TITLE					
PG PREMIUM,CBL-SUPPORT,4-HOLE						SCALE					
1:5						DOCUMENT NO.					
PGP-CS04						ECN 40171556CMO					
SIZE		Auth Group		INSL		MODEL		DRAWING		SHEET	
C		⊕		◁		VERSION		STATUS		REVISION	
01		RE		B		02		RE		C	