# MLOC-4-F1XM-HM-10M



HELIAX® M-LOC Multiport cluster 4 ports SureFlex® cable assembly with interface type M-LOC latching male to 4.3-10 male,size 1/4", length 10 meters

### Product Classification

Product Type	HELIAX® MLOC cluster, SureFlex® D-CLASS, dynamic PIM
Product Brand	HELIAX®   SureFlex®
Product Series	MLOC
General Specifications	
Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	M-LOC Male

4.3-10 Male

А

#### Interface, Connector B **Specification Sheet Revision Level**

### Dimensions

Length	10 m   32.808 ft
Nominal Size	1/4 in
Electrical Specifications	

3rd Order IMD Dynamic	-119 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

## VSWR/Return Loss

Frequency Band	Gated VSWR	Gated Return Loss (dB)	Insertion Loss, typical (dB)
1000-3000 MHz	1.065	30	1.89
3000–4200 MHz	1.106	26	2.28

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 25, 2023



## MLOC-4-F1XM-HM-10M

4200–5000 MHz	1.119	25	2.51
Mechanical Specifications			
Minimum Bend Radius, multiple Bend	<b>s</b> 25.4 mm	1 in	
Minimum Bend Radius, single Bend	25.4 mm	1 in	
Minimum Bend Radius, multiple Bend	<b>s</b> 25.4 mm		

## Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Immersion Test Method	Meets IEC 60529:2001, IP68 in mated condition

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 25, 2023

