760256446 | TENIO-C6H-START



TENIO™ C6 288f Distribution closure STARTer kit with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

Suitable for all splice closure applications with maximum capacity of 288 fibres. This basic kit contains a full set of blanking seals, onefeeder cable seal kit, cable termination units to install a loop-through feeder. Full set of splice trays for up to 288f splices. Please selectdistribution seal kits, CTU's and splitters from our ordering guide. This kit contains a MOBRA bracket suitable for use with PIAchambers. Fibre trays and seal kits are pre-assembled into the closure in the factory to reduce engineering time in the field.

Product Classification

Regional Availability EMEA

Product Type Single-ended, rectangular fiber closure

Product Brand TENIO™
Product Series TENIO

General Specifications

Cable Entry Drop Port StyleGel blockCable Entry Main Port StyleGel block

Cable Ports Quantity, total 6 multi-out ports (30 cables)

Cable Sealing Type Compressed gel

Closure Sealing Type Side latch

Closure Style Single-ended

Color Black

Flash Test Valve Pre-installed

Mounting Wall

Network Area Type Distribution | Drop

Splice Tray Included, quantity 12

Splice Tray Type Included 24-fiber, single element

Splices per Tray, quantity 24
Splicing Capacity, Single Fusion, maximum 288

Splicing Type, Supported Single fusion



760256446 | TENIO-C6H-START

Dimensions


 Height
 230 mm | 9.055 in

 Width
 134 mm | 5.276 in

 Length
 449 mm | 17.677 in

 Main Cable Diameter, maximum
 16 mm | 0.63 in

Ordering Tree



Material Specifications

Material Type Impact-resistant polymer

Environmental Specifications

Environmental SpaceBelow ground| BuriedQualification StandardsIEC 61300, 2 m waterhead

Water Resistance Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity

Packaging TypeBox| CartonWeight, net1 kg| 2.205 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

COMMSCOPE®

760256446 | TENIO-C6H-START

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

760236356 TENIO-C6H-SLE-12-V

760244933

CTU-L

760250714

TENIO-MOBRA-TUBE-45x45

CV6797-000 TENIO-SKG3-7/10

CW8862-000 TENIO-SKG-DUMMY TENIO™ High Density Fiber Optic Splice Closure, Gel Cable sealing, 12 pre-installed 24-splice

trays, with test valve

Fiber Closure Cable Termination Unit, Large for up to 16 mm diamter cables

TENIO™ Mounting bracket for arm mounting

TENIO™ Cable Gel Seal kit, 3 cable outlets, 7 to 10 mm diameter per cable outlet

TENIO™ Cable Gel Seal kit, dummy, no cable outlets, black

