

FFVV-65B-R2-HG



8-port sector antenna, 4x 617-894 and 4x 1695-2690 MHz, 65° HPBW, 2x RET

- Antenna design optimized to offer high gain performances
- Broadband performance 617-894 MHz and 1695-2690 MHz

General Specifications

Antenna Type	Sector
Band	Multiband
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, mid band	4
RF Connector Quantity, low band	4
RF Connector Quantity, total	8

Remote Electrical Tilt (RET) Information


RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Input Voltage	10–30 Vdc
Internal RET	Low band (1) Mid band (1)
Power Consumption, active state, maximum	10 W
Power Consumption, idle state, maximum	2 W
Protocol	3GPP/AISG 2.0 (Single RET)

Dimensions

Width	640 mm 25.197 in
Depth	235 mm 9.252 in
Length	1828 mm 71.969 in
Net Weight, antenna only	45.2 kg 99.649 lb

FFVV-65B-R2-HG

Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG No.	AISG RET UID
R1	617-894	1 - 2	1	AISG1	CPxxxxxxxxxxxxxxxxR1
R2	617-894	3 - 4			
Y1	1695-2690	5 - 6	2	AISG1	CPxxxxxxxxxxxxxxxxY1
Y2	1695-2690	7 - 8			

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 617 – 894 MHz
Polarization	±45°
Total Input Power, maximum	900 W @ 50 °C

FFVV-65B-R2-HG

Electrical Specifications

	R1,R2	R1,R2	R1,R2	Y1,Y2	Y1,Y2	Y1,Y2	Y1,Y2	Y1,Y2
Frequency Band, MHz	617-698	698-806	806-894	1695-1880	1850-1990	1920-2200	2300-2500	2500-2690
RF Port	1-4	1-4	1-4	5-8	5-8	5-8	5-8	5-8
Gain, dBi	14.5	15.1	15.9	18.4	18.8	19.1	19.4	19.6
Beamwidth, Horizontal, degrees	67	64	58	65	58	60	52	51
Beamwidth, Vertical, degrees	12.8	11.5	10.5	5.1	4.8	4.5	4	3.8
Beam Tilt, degrees	2-12	2-12	2-12	2-9	2-9	2-9	2-9	2-9
USLS (First Lobe), dB	18	17	15	16	18	18	17	17
Front-to-Back Ratio at 180°, dB	29	33	34	37	39	37	33	31
Isolation, Cross Polarization, dB	25	25	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	250	250	250	200	200	200	200	200

Electrical Specifications, BASTA

	617-698	698-806	806-894	1695-1880	1850-1990	1920-2200	2300-2500	2500-2690
CPR at Boresight, dB	16	17	17	20	23	20	22	19

Mechanical Specifications

Wind Loading @ Velocity, frontal	715.0 N @ 150 km/h (160.7 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	206.0 N @ 150 km/h (46.3 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	911.0 N @ 150 km/h (204.8 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	446.0 N @ 150 km/h (100.3 lbf @ 150 km/h)
Wind Speed, maximum	241.4 km/h (150 mph)

Packaging and Weights

Width, packed	752 mm 29.606 in
Depth, packed	387 mm 15.236 in
Length, packed	1982 mm 78.032 in

FFVV-65B-R2-HG

Weight, gross

58.4 kg | 128.75 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

BSAMNT-2F

- Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

* Footnotes

Performance Note

Severe environmental conditions may degrade optimum performance