


# SA-BL

---

## Stiff Arm Bracket for 2-3/8 in OD pipe



### Product Classification

**Product Type** Stiff arm mount

### General Specifications

**Mounting** Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

**Pipe, quantity** 0

### Dimensions

**Height** 152.4 mm | 6 in

**Width** 203.2 mm | 8 in

**Length** 152.4 mm | 6 in

**Mounting Diameter, maximum** 203.2 mm | 8 in

**Mounting Diameter, minimum** 50.8 mm | 2 in

**Pipe Outer Diameter** 0 mm | 0 in

### Material Specifications

**Material Type** Hot dip galvanized steel

### Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

### Packaging and Weights

**Included** Attachment hardware | Clamps

**Packaging quantity** 1

**Weight, net** 9.117 kg | 20.1 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS



### Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted

## \* Footnotes

### Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code