

Copper Cable, category 3, 25 pair, U/UTP, CMR rated, 1000 ft, gray



- Exceptional 100-Ohm series cables for both analog and digital services
- Meets or exceeds industry requirements and environmental regulations
- Small outside diameter and cross-sectional area in bundles and cable
- Innovative design and enhanced electrical and mechanical performance

OBSOLETE

This product was discontinued on: August 31, 2022

Replaced By:

1499418-2 1061F SLT C5E 25/24 U/UTP R1000 1061F Cat5e U/UTP Cable, Riser, Slate Jacket, 25 pair count, 1000 ft (305 M) length reel

Product Classification

Regional Availability	Asia
Portfolio	NETCONNECT®
Product Type	Twisted pair cable
Product Series	310 Series

General Specifications

ANSI/TIA Category	3
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	50
Jacket Color	Gray
Pairs, quantity	25
Transmission Standards	ANSI/TIA-568.2-D CENELEC EN 50288-6-1 ISO/IEC 11801 Class E

Dimensions


Cable Length	304.8 m 1000 ft
Diameter Over Jacket, nominal	8.992 mm 0.354 in

1859363-4

Conductor Gauge, singles

26 AWG

Cross Section Drawing



Electrical Specifications

Characteristic Impedance	100 ohm
Characteristic Impedance Tolerance	±15 ohm
dc Resistance, maximum	14 ohms/100 m 4.267 ohms/100 ft
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Operating Voltage, maximum	80 V

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	PVC

Mechanical Specifications

Minimum Bend Radius, multiple Bends	36 mm 1.417 in
--	------------------

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)

1859363-4

Flame Test Method

NEC Article 800 | UL 444

Packaging and Weights

Packaging Type

Reel

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

