


MC-HP14M-12-96-HD



3-Sector Monopole Co-location Platform Kit, 12 in to 50 in OD, 14 ft 6 in face, includes twelve 2-7/8" x 96 in pipes

Product Classification

Portfolio	CommScope®
Product Type	Co-location platform
Ordering Note	CommScope® standard product (Global)
Warranty	One year

General Specifications

Mounting	Monopole, 304.8–1270 mm (12–50 in) OD
Pipe, quantity	12
Sectors, quantity	3

Dimensions

Height	2,438.4 mm 96 in
Face Width	4.42 m 14.5 ft
Width	4,419.6 mm 174 in
Pipe Length	2,438.4 mm 96 in
Mounting Diameter, maximum	1270 mm 50 in
Mounting Diameter, minimum	304.8 mm 12 in
Pipe Outer Diameter	73.152 mm 2.88 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating Test Method	TIA-5053 TIA/EIA-222
--------------------------------	------------------------

MC-HP14M-12-96-HD

Packaging and Weights

Included	Plain end pipes (12) Platform Rail Ring mount
Packaging quantity	1
Weight, net	903.556 kg 1992 lb

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines