810010321/DB | 0-144-L2-8W-M12BK/20G



LightScope ZWP® Double Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable

• Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	0-L2
General Specifications	
Armor Type	Corrugated steel
Cable Type	Stranded loose tube
Construction Type	Armored
Subunit Type	Gel-filled
Inner Jacket Color	Black
Jacket Color	Black
Jacket Marking	Meters
Subunit, quantity	12
Fibers per Subunit, quantity	12
Total Fiber Count	144
Dimensions	
Buffer Tube/Subunit Diameter	2 mm 0.079 in
Diameter Over Inner Jacket	15 mm 0.591 in
Diameter Over Jacket	20.4 mm 0.803 in


Representative Image

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 17, 2024



810010321/DB | 0-144-L2-8W-M12BK/20G



Material Specifications

Jacket Material	PE
Inner Jacket Material	PE
Mechanical Specifications	
Minimum Bend Radius, loaded	408 mm 16.063 in
Minimum Bend Radius, unloaded	306 mm 12.047 in
Tensile Load, long term, maximum	1800 N 404.656 lbf
Tensile Load, short term, maximum	4000 N 899.236 lbf
Compression	40 N/mm 228.406 lb/in
Compression Test Method	IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	IEC 60794-1 E6
Impact	10 N-m 88.507 in lb
Impact Test Method	IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1 E1

Optical Specifications

Fiber Type

G.652.D and G.657.A1

Optical Specifications, Wavelength Specific

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 17, 2024



810010321/DB | 0-144-L2-8W-M12BK/20G

Standards Compliance

ITU-T G.652.D | ITU-T G.657.A1

Environmental Specifications

Installation temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	IEC 60794-1-2
EN50575 CPR Cable EuroClass Fire Performance	Fca
Environmental Space	Buried
Jacket UV Resistance	UV stabilized
Water Penentration	24 h
Water Penentration Test Method	IEC 60794-1 F5

Environmental Test Specifications

Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1 F1

Packaging and Weights

Cable weight

371 kg/km | 249.3 lb/kft

Included Products

DB-8W-LT – LightScope ZWP® Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 17, 2024

