


AL4RPV-50W



AL4RPV-50, HELIAX® Plenum Rated Air Dielectric Coaxial Cable, corrugated aluminum, 1/2 in, off white PVC jacket.

- This product is part of the CommScope Wired for Wireless® Solution

Product Classification

Product Type	Air coaxial cable
Product Brand	HELIAX®
Product Series	AL4-50
Ordering Note	CommScope® standard product (Global)

General Specifications

Product Number	529279903/00
Flexibility	Standard
Jacket Color	Off-white

Dimensions

Diameter Over Jacket	15.748 mm 0.62 in
Inner Conductor OD	4.572 mm 0.18 in
Outer Conductor OD	14.046 mm 0.553 in
Nominal Size	1/2 in

Electrical Specifications

Cable Impedance	50 ohm ±2 ohm
Capacitance	75.459 pF/m 23 pF/ft
dc Resistance, Inner Conductor	1.575 ohms/km 0.48 ohms/kft
dc Resistance, Outer Conductor	1.575 ohms/km 0.48 ohms/kft
dc Test Voltage	4000 V
Inductance	0.19 µH/m 0.058 µH/ft
Insulation Resistance	100000 MOhms-km
Jacket Spark Test Voltage (rms)	5000 V
Operating Frequency Band	1 – 6000 MHz
Peak Power	40 kW

AL4RPV-50W

Power Attenuation	2.325
Pulse Reflection	0.5%
Velocity	88 %

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.216	0.066	35.37
1.5	0.264	0.081	28.84
2.0	0.306	0.093	24.95
10.0	0.691	0.211	11.04
20.0	0.985	0.3	7.75
30.0	1.213	0.37	6.29
50.0	1.581	0.482	4.83
85.0	2.087	0.636	3.66
88.0	2.126	0.648	3.59
100.0	2.274	0.693	3.35
108.0	2.368	0.722	3.22
150.0	2.821	0.86	2.7
174.0	3.054	0.931	2.5
200.0	3.292	1.003	2.32
204.0	3.327	1.014	2.29
300.0	4.104	1.251	1.86
400.0	4.808	1.465	1.59
450.0	5.134	1.565	1.49
460.0	5.197	1.584	1.47
500.0	5.445	1.659	1.4
512.0	5.517	1.682	1.38
600.0	6.032	1.839	1.26
700.0	6.583	2.007	1.16
800.0	7.105	2.166	1.07
824.0	7.227	2.203	1.06
894.0	7.574	2.308	1.01
960.0	7.892	2.405	0.97
1000.0	8.081	2.463	0.94
1218.0	9.068	2.764	0.84

AL4RPV-50W

1250.0	9.207	2.806	0.83
1500.0	10.256	3.126	0.74
1700.0	11.053	3.369	0.69
1794.0	11.416	3.48	0.67
1800.0	11.439	3.487	0.67
2000.0	12.192	3.716	0.63
2100.0	12.559	3.828	0.61
2200.0	12.92	3.938	0.59
2300.0	13.276	4.046	0.57
2500.0	13.975	4.259	0.55
2700.0	14.656	4.467	0.52
3000.0	15.649	4.77	0.49
3400.0	16.928	5.159	0.45
3600.0	17.551	5.349	0.43
3700.0	17.859	5.443	0.43
3800.0	18.164	5.536	0.42
3900.0	18.467	5.628	0.41
4000.0	18.768	5.72	0.41
4100.0	19.066	5.811	0.4
4200.0	19.363	5.902	0.39
4300.0	19.658	5.991	0.39
4400.0	19.951	6.081	0.38
4500.0	20.241	6.169	0.38
4600.0	20.531	6.257	0.37
4700.0	20.818	6.345	0.37
4800.0	21.104	6.432	0.36
4900.0	21.388	6.519	0.36
5000.0	21.671	6.605	0.35
6000.0	24.42	7.443	0.31

Material Specifications

Dielectric Material	PE spline
Jacket Material	PVC
Inner Conductor Material	Copper-clad aluminum wire
Outer Conductor Material	Corrugated aluminum

AL4RPV-50W

Mechanical Specifications

Minimum Bend Radius, multiple Bends	127 mm 5 in
Minimum Bend Radius, single Bend	63.5 mm 2.5 in
Number of Bends, minimum	15
Tensile Strength	79 kg 174.165 lb
Bending Moment	5 ft lb 6.779 N-m
Flat Plate Crush Strength	1.429 kg/mm 80 lb/in

Environmental Specifications

Installation temperature	-5 °C to +60 °C (+23 °F to +140 °F)
Operating Temperature	-20 °C to +85 °C (-4 °F to +185 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +185 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C
Fire Retardancy Test Method	NFPA 262/CATVP/CMP

Packaging and Weights

Cable weight	0.208 kg/m 0.14 lb/ft
---------------------	-------------------------

Regulatory Compliance/Certifications

Agency	Classification
c(ETL)us Certification	CATVP/CMP
CHINA-ROHS	Below maximum concentration value
ETL Certification	CATVP/CMP
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

