




1.0 GENERAL NOTES  
 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X]  
 1.2 FOR PATENT INFO: <https://www.cs-pat.com>

2.0 DESIGN NOTES  
 2.1 ANY HAZARDS OR OBSTRUCTIONS TO THE CLIMBING FACILITY AND SAFETY CLIMB MUST BE IDENTIFIED PRIOR TO INSTALLING THE APPURTENANCE. ADDITIONAL PRODUCTS MAY BE REQUIRED TO MAINTAIN THE INTEGRITY OF THE SAFETY CLIMB. DURING INSTALLATION, TEMPORARY AND/OR PERMANENT PRECAUTIONARY MEASURES SHOULD BE TAKEN TO PRESERVE THE CLIMBING FACILITY AND/OR SAFETY CLIMB.

3.0 MANUFACTURING/SPECIAL REQUIREMENTS  
 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.

4.0 TEST  
 5.0 PACKAGING  
 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005  
 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER  
 5.3 EXTRA HARDWARE MAYBE SUPPLIED, BAGGED AND SHIPPED

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	RY1002 23OCT23	EB1063 40181149CMO
B	QTY FOR 9674-1(ITEM 2) & GWL-05(ITEM 4) WAS 1EA, GWF05A(ITEM 3) & GN-05(ITEM 5) WAS 2EA; ADDED NOTE FOR EYEBOLT; CHG BOX FROM BX92 TO BXGB2	RY1002 19FEB24	EB1063 40188637CMO



NOTE: -ANY ARRANGEMENTS OF THE EYEBOLTS IS ACCEPTABLE  
 -MAXIMUM LOADING CAPACITY PER EYEBOLT = 1000 LBS  
 -MAXIMUM LOADING CAPACITY IN ANY COMBINATION = 1000 LBS  
 -NOT TO BE USED FOR HOISTING  
 -CABLE LADDER TO BE INSPECTED BY COMPETENT PERSON TO ENSURE PROPER INSTALLATION PRIOR TO INSTALL  
 -DESIGNED TO BE UTILIZED ON "CL-0610-U" OR "CL-0620-U"

COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;  
 INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT	NOTE NO.
1	MTC4164-020-00	20 INCH CROSSMEMBER GALV	1	6.14 LBS	
2	9674-1	BOLT,EYE,5/8X3,STL,ZN PLD	2	0.08 LBS	
3	GWF05A	GALV FLAT WASHER HARDENED 5/8", 1.30D	4	0.04 LBS	
4	GWL-05	5/8" GALV LOCK WASHER	2	0.03 LBS	
5	GN-05	5/8" GALV HEX NUT	4	0.08 LBS	
6	GB-03145	3/8" X 1-1/2" GALV BOLT KIT	2	0.07 LBS	
7	HKCLU.02	BACKING PLATE	2	0.95 LBS	
8	GJB0380	8" GALV J-BOLT KIT	4	0.23 LBS	
9	GN-03	3/8" GALV HEX NUT	4	0.02 LBS	
10	GWL-03	3/8" GALV LOCK WASHER	4	0.01 LBS	
11	GWF-03	3/8" GALV FLAT WASHER	4	0.01 LBS	
12	MTC4164-LAB01	LABEL, GRIP ANCHOR, CABLE LADDER,006	1	0.01 LBS	

<b>COMMSCOPE, INC. OF NORTH CAROLINA</b>			
TOLERANCES		SAP MATERIAL MASTER	
1 PLACE .X[X] ± 0.2[6.3]	3 PLACE .XXX[X] ± 0.060[1.5]	860674608-006	
2 PLACE .XX[X] ± 0.12[3.0]	ANGLES ± 2°		
FINISH		MATERIAL	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	NAME	DATE	TITLE
	CE RY1002	23OCT23	<b>GRIP ANCHOR, CABLE LADDER,006</b>
	RW RY1002	02/21/2024	
	AD EB1063	02/26/2024	
	RE LMCOWEL	03/05/2024	
ECN 40188637CMO			
SCALE	DOCUMENT NO.		
<b>1:3</b>	<b>860674608-006</b>		
SIZE	Auth Group	INSL	MODEL
<b>C</b>			
VERSION	STATUS	REVISION	VERSION
01	RE	A	01
DRAWING		REVISION	SHEET
		RE	1 OF 2


DENSITY	9.98	lbs/in <sup>3</sup>
MASS	9.98	lbs
VOLUME	39.24	in <sup>3</sup>
SURFACE AREA	365.17	in <sup>2</sup>
HEIGHT	8.25"	
LENGTH	19.64"	
WIDTH		

4


3

2


1



ANGLE MEMBER SET-UP



ROUND MEMBER SET-UP



NOTE: -ANY ARRANGEMENTS OF THE EYEBOLTS IS ACCEPTABLE  
 -MAXIMUM LOADING CAPACITY PER EYEBOLT = 1000 LBS  
 -MAXIMUM LOADING CAPACITY IN ANY COMBINATION = 1000 LBS  
 -NOT TO BE USED FOR HOISTING  
 -CABLE LADDER TO BE INSPECTED BY COMPETENT PERSON TO ENSURE PROPER INSTALLATION PRIOR TO INSTALL  
 -DESIGNED TO BE UTILIZED ON "CL-0610-U" OR "CL-0620-U"

COMMSCOPE, INC. OF NORTH CAROLINA				
TITLE GRIP ANCHOR, CABLE LADDER,006				
SIZE C	SCALE 1:5	DOCUMENT NO. 860674608-006		
DRAWING		REVISION		SHEET
VERSION 01	STATUS RE	REVISION B	2 OF 2	

4

3

2

1